



## Main

Product or component type	All-In-One
Range of product	QO
Meter socket type	Ringed
Hub type	A-L

## Complementary

Line Rated Current	200 A
Number of Phases	1 phase
Short-circuit current	22 kA
Mounting	Semi flush
Number of spaces	30
Number of circuits	42
Number of Tandem Breakers	12
Electrical connection	Lugs line side Lugs service ground
Wire Size	AWG 12...AWG 2/0 aluminium)service ground AWG 4...250 kcmil aluminium/copper)line side AWG 14...AWG 2/0 copper)service ground
Tightening torque	Main lugs: 250 lb.in, AWG 4...250 kcmil, aluminium/copper Service ground 50 lb.in, AWG 14...AWG 2/0, copper Service ground 50 lb.in, AWG 12...AWG 2/0, aluminium Branch lugs 50 lb.in, AWG 14...AWG 4, copper Branch lugs 50 lb.in, AWG 12...AWG 2, aluminium Branch lugs 35 lb.in, AWG 6...AWG 4, aluminium/copper Branch lugs 25 lb.in, AWG 8, aluminium/copper Branch lugs 20 lb.in, AWG 14...AWG 10, aluminium/copper Branch lugs 20 lb.in, AWG 12...AWG 10, aluminium/copper Cover 10 lb.in
Disconnect	Service disconnect (factory installed)
Disconnect Rating	225 A
Branch Breaker Rating	200 A
Service feed location	OH with field installed tunnel kit UG
Bypass type	No bypass
Connections - terminals	Plug-on neutral
Product compatibility	Solar ready
Width	16.80 in (426.72 mm)
Depth	3.40 in (86.36 mm)
Height	39.80 in (1010.92 mm)

## Ordering and shipping details

Category	00148 - HOMELINE CSED DEVICES
Discount Schedule	DE3A
GTIN	00785901109549
Nbr. of units in pkg.	1
Package weight(Lbs)	63.3 lb(US) (28.71 kg)
Returnability	Yes

## Packing Units

Package 1 Height	0.63 ft (0.191 m)
Package 1 width	1.47 ft (0.447 m)
Package 1 Length	3.79 ft (1.156 m)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>