

Product data sheet

Characteristics

HOM60120L225PC

Load center, Homeline, 1 phase, 60 spaces,
120 circuits, 225A convertible main lugs, PoN,
NEMA1, combo cover



Main

Product Type	Load Center
Marketing Trade Name	Homeline
Load Center Type	Main lugs
Rated Current	225 A
Number of Spaces	60
Maximum Number of Single Pole Circuits	120
Enclosure Rating	NEMA 1 for indoor
Cover Type	Combination flush/surface cover
Electrical Connection	Lugs

Complementary

Max Short Circuit Current Rating	10 kA
Maximum Number of Tandem Breakers	60
Number of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 4...250 kcmil copper AWG 4...300 kcmil aluminium
Ground Bar	Grounding bar (ordered separately)
Wiring Configuration	3-wire
Busbar Material	Tin plated aluminium busbar
Enclosure Material	Welded sheet steel
Surface Finish	Baked enamel grey
Box Number	25
Height	48.62 in (1235 mm)
Depth	3.74 in (95 mm)
Width	14.25 in (362 mm)

Environment

Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL listed file E-6294

Ordering and shipping details

Category	00045 - HOM LC&CVR,12-42 CKT,NEMA1
Discount Schedule	DE3C
GTIN	00785901974314
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	0.54 ft (0.165 m)
Package 1 width	1.38 ft (0.422 m)
Package 1 Length	4.32 ft (1.316 m)