

Main

Range	9080LB
Product	Miniature Power Distribution Block
Current Rating	115 A copper 90 A aluminium
Short Circuit Current Rating	65 kA

Complementary

Voltage Rating	600 V AC/DC
Mounting Type	Surface mount
Number of poles	3
Terminals per Pole	1 line 1 load
Wire Size	Line 1, AWG 14...AWG 2, copper or aluminium Load 1, AWG 14...AWG 2, copper or aluminium
Electrical Connection	Tin plated aluminium lugs
SCCR	100 kA UL 508 A
Ambient Air Temperature for Operation	-40...125 °C (-40...257 °F)
Block Material	Thermoplastic: block
Terminal Tightening Torque	Line lug 50 lbf.in (5.6 N.m) AWG 3...AWG 2 copper or aluminium Line lug 45 lbf.in (5.08 N.m) AWG 6...AWG 4 copper or aluminium Line lug 40 lbf.in (4.5 N.m) AWG 8 copper or aluminium Line lug 35 lbf.in (4.0 N.m) AWG 12...AWG 10 copper or aluminium Line lug 35 lbf.in (4.0 N.m) AWG 14 copper Load lug 50 lbf.in (5.6 N.m) AWG 3...AWG 2 copper or aluminium Load lug 45 lbf.in (5.08 N.m) AWG 6...AWG 4 copper or aluminium Load lug 40 lbf.in (4.5 N.m) AWG 8 copper or aluminium Load lug 35 lbf.in (4.0 N.m) AWG 12...AWG 10 copper or aluminium Load lug 35 lbf.in (4.0 N.m) AWG 14 copper
Wire stripping length	Line: 0.5 in (12.7 mm)
Height	2.29 in (58.17 mm)
Width	2.12 in (53.85 mm)
Depth	1.62 in (41.15 mm)
End Barrier	9080LB13

Environment

Certifications	UL recognized E60616 CCN XCFR2[RETURN]CE[RETURN]CSA file 70361 class 6228 01
----------------	--

Ordering and shipping details

Category	US10CP121711
Discount Schedule	OCP1
GTIN	785901097426
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.300 in (5.842 cm)
Package 1 Width	1.50 in (3.81 cm)
Package 1 Length	2.100 in (5.334 cm)
Package 1 Weight	3.52 oz (99.79 g)

Offer Sustainability

California proposition 65	"WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov "
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------