

# Product data sheet

## Characteristics

# PK7GTA

Load center accessory, QO/Homeline, ground bar kit, 7 terminals



### Main

|              |     |
|--------------|-----|
| Product line | QO  |
| Product type | Bar |

### Complementary

|                           |   |
|---------------------------|---|
| Number of connectors      | 7   |
| Wire size                 | AWG 14...AWG 4 copper<br>AWG 12...AWG 4 aluminium   |
| Provided equipment        | 2 screw   |
| Bar length                | 2.9 in (73 mm)  |
| Maximum length of segment | 1.3 in (32 mm)  |
| Device mounting           | Direct mounting back of enclosure   |
| Height                    | 0.437 in (11.100 mm)  |
| Depth                     | 0.312 in (7.925 mm)   |
| Tightening torque         | 30 lb.in<br>Mounting screw 30 lb.in<br>20 lb.in, AWG 14...AWG 10, copper<br>20 lb.in, AWG 12...AWG 10, aluminium<br>35 lb.in, AWG 6...AWG 4<br>25 lb.in, AWG 8<br>25 lb.in, AWG 14...AWG 12, copper<br>25 lb.in, AWG 12...AWG 10, aluminium |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

### Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US1DE3A00102 |
| Discount Schedule | DE3A         |
| GTIN              | 785901026372 |
| Returnability     | Yes          |
| Country of origin | US           |

### Packing Units

|                              |                              |
|------------------------------|------------------------------|
| Unit Type of Package 1       | PCE                          |
| Number of Units in Package 1 | 1                            |
| Package 1 Height             | 0.300 in (0.762 cm)          |
| Package 1 Width              | 5.0000000000 in (12.700 cm)  |
| Package 1 Length             | 10.0000000000 in (25.400 cm) |
| Package 1 Weight             | 1.280 oz (36.287 g)          |
| Unit Type of Package 2       | CAR                          |
| Number of Units in Package 2 | 10                           |
| Package 2 Height             | 4.0000000000 in (10.160 cm)  |

|                  |                              |
|------------------|------------------------------|
| Package 2 Width  | 6.500 in (16.510 cm)         |
| Package 2 Length | 10.0000000000 in (25.400 cm) |
| Package 2 Weight | 16.000 oz (453.592 g)        |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>                      |
| REACH Regulation           |  <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  |
| Mercury free               | Yes   |
| RoHS exemption information |  Yes   |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a> |
| Circularity Profile        | No need of specific recycling operations  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|