

# Product data sheet

## Characteristics

# QU816D400SL

Meter mains, QO, combination service entrance, ringless socket, 400A, surface mount, maximum 8 spaces, 16 circuits, class 320 lever bypass



### Main

Product or component type	Meter Mains
Range of product	QO

### Complementary

Line Rated Current	400 A
Short-circuit current	25 kA
Network number of phases	1
Meter socket type	Ringless
Mounting	Surface
Number of spaces	8
Number of circuits	16
Number of Tandem Breakers	8
Hub type	A-L
Electrical connection	Studs line side Feed-thru lugs service ground
Wire Size	AWG 4...250 kcmil aluminium)service ground AWG 4...250 kcmil copper)service ground
Disconnect	Service disconnect (factory installed)
Main Breaker Rating	200 A
Branch Breaker Rating	200 A
Service feed location	UG
Bypass type	Class 320 lever bypass
Height	43.00 in (1092.20 mm)
Width	28.25 in (717.55 mm)
Depth	7.87 in (199.90 mm)

### Environment

Product certifications	UL E-6294
------------------------	-----------

### Ordering and shipping details

Category	00022 - QO METER MAINS
Discount Schedule	DE3A
GTIN	00785901468455
Nbr. of units in pkg.	1
Package weight(Lbs)	115 lb(US) (52.16 kg)

Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	0.80 ft (0.244 m)
Package 1 width	2.44 ft (0.744 m)
Package 1 Length	3.51 ft (1.069 m)

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

### Contractual warranty

Warranty	18 months
----------	-----------