

Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 15A 125V, 5-15R and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL5269C](#)



Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2- Pole 3-Wire Grounding, 15A 125V, 5-15R, Black and White, Single Pack.

Application

- Industrial/Commercial Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL5269C
Color	Black, White
Cord Range	0.300"-0.660" (7.6-16.8)
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Insulation	Insulated Body
Item Type	Insulgrip Plug
Material	Polycarbonate
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Insulgrip®
Specifications	<ul style="list-style-type: none"> Assembly Screws - Nickel plated steel Contact Holder - Nylon Contacts - .040 in. (1.0) Brass Housing/Cord Clamp - Nylon

Style	Standard
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Type	Connector Body
UPC	783585173252

Dimensions

Dimensions	2.65 in x 1.55 in x 2.65 in
Display Size	Standard
Height	2.65 in
Length	2.65 in
Weight	0.15 lb
Width	1.55 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#18 AWG to #10 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> CSA Certified to C22.2 No. 42 File 280 NEMA® WD-6 Compliant
----------------------	--

- Terminal Clamp - Nickel plated steel
- Terminal Retainer - Clear Polycarbonate
- Terminal Screws - #8-32 Brass , multiple drive

- UL Listed to UL498 File E1706

Carton Quantity 10
Pallet Quantity 6600

Nema Rating 5-15R
Standards - RoHS Compliance CM
Status

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL5269C](#)
[Warranty - Industrial & Commercial Products](#)

Logistics



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL5269C-SPEC-EN | REV 10/2024