

2510MBG2

Manual starter, integral horsepower, NEMA M0, 600VAC, 3 pole, 5HP at 380/575VAC, 3 phase, no indicator, NEMA 1

Main

Product	Manual Starter
Type	M
NEMA Size	M-0

Complementary

Control Unit	Push-button
Pilot Light	No indicator
Horsepower Rating	3 Hp 200...230 V AC, 3 phase 5 hp 380...575 V AC, 3 phase
Voltage Rating	600 V AC
Number of Poles	3P
Starter Type	Non reversing
Electrical Connection	Pressure wire clamp
Overload Relay Type	Melting alloy
Number of Thermal Units Required	3
Wire Gauge	AWG 14...AWG 8 copper
Auxiliary Contacts	Without
Height	8.63 in (219.20 mm)
Width	5 in (127.0000000000 mm)
Depth	4.13 in (104.90 mm)
Net Weight	4.14 lb(US) (1.88 kg)

Environment

Certifications	CSA LR60905 class 3211 05[RETURN]JUL listed file E42243 CCN NLRV
NEMA Enclosure Rating	NEMA 1 painted sheet steel

Ordering and shipping details

Category	US10CP121103
Discount Schedule	OCP1
GTIN	785901792536
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.700 in (11.938 cm)
Package 1 Width	5.600 in (14.224 cm)
Package 1 Length	9.200 in (23.368 cm)
Package 1 Weight	4.101 lb(US) (1.860 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	126
Package 2 Height	40.0000000000 in (101.600 cm)
Package 2 Width	40.0000000000 in (101.600 cm)
Package 2 Length	48.0000000000 in (121.920 cm)
Package 2 Weight	535.0006 lb(US) (242.672 kg)

Offer Sustainability

California proposition 65	"WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov "
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------