

ELITE



MODEL AL2240MG

TYPE IAA

375 LBS
LOAD CAPACITY

(Includes weight of user plus materials)


ALUMINUM ATTIC LADDER

**NEW
PRODUCT**




WITH
INSULATION
PACKAGE AND
WIDER
CLEARANCE

**22" WIDE
OPENING**



T-HANDLE
FOR EASY
ACCESS



WEATHER STRIPPING
THAT **REDUCES**
ENERGY LOSS



LOUISVILLE.
LADDER

**BUILT TO
BE
ABOVE**

ANSI
Meets or exceeds requirements
of American National Standards Institute
ANSI A14.9



ELITE



MODEL AL2240MG



1 Lighter Aluminum Frame
Pre-drilled holes for easier installation.



2 Smooth Operation
Easier to open and close. Door with gas piston system.



3 Energy Efficiency
Weather stripping that reduces energy loss.



4 Adjustable Shoes
Fits heights 7-ft 8 in to 10-ft 3-in.



5 Safety
Aluminum handrail for a comfortable transition.



AL2240MG FLYER 2023 © Louisville Ladder, Inc. All rights reserved.



MODEL	FITS CEILING HEIGHTS		ROUGH OPENING	APPROX. LANDING SPACE	SWING CLEARANCE	STEP DEPTH	APPROX. WEIGHT (LBS)	APPROX. CUBES (FT)
	MIN	MAX						
AL2240MG	7' 8"	10' 3"	22.5" X 54"	67"	74"	3"	40.8	6.6



WWW.LOUISVILLELADDER.COM

