

ELITE



MODEL AL2540MG

TYPE IAA

375 LBS
LOAD CAPACITY

(Includes weight of user plus materials)



ALUMINUM ATTIC LADDER

NEW
PRODUCT



WITH
INSULATION
PACKAGE AND
WIDER
CLEARANCE

25" WIDE
OPENING



WEATHER STRIPPING
THAT **REDUCES**
ENERGY LOSS



LOUISVILLE
LADDER

BUILT TO
BE
ABOVE

ANSI
Meets or exceeds requirements
of American National Standards Institute
ANSI A14.9



ELITE



MODEL AL2540MG



1 Lighter Aluminum Frame
Pre-drilled holes for easier installation.



2 Smooth Operation
Easier to open and close. Door with gas piston system.




3 Energy Efficiency
Weather stripping that reduces energy loss.



4 Adjustable Shoes
Fits heights 7-ft 8 in to 10-ft 3-in.



5 Safety
Aluminum handrail for a comfortable transition.



AL2540MG FLYER 2023 © Louisville Ladder, Inc. All rights reserved.

MODEL	FITS CEILING HEIGHTS		ROUGH OPENING	APPROX. LANDING SPACE	SWING CLEARANCE	STEP DEPTH	APPROX. WEIGHT (LBS)	APPROX. CUBES (FT)
	MIN	MAX						
AL2540MG	7' 8"	10' 3"	25.5" X 54"	67"	74"	3"	43.8	7.6



WWW.LOUISVILLELADDER.COM

