PORCELAIN PLUS for HARD TILES

- Cobalt tungsten carbide tip is ideal for drilling porcelain tiles up to a scratch hardness of 8
- Unique 4-face point grinding extends drill bit life
- Flat bottom parabolic flute ensures fast and efficient removal of the drill dust and prevents clogging
- Drill bit shank is made from the finest chrome vanadium steel
- with excellent centerina prevents walking - tape or center punching no longer needed
- Diamond ground PORC+ cuts nice. clean holes with very little or no chipping





Drilling Tips

- Tile should be on a level surface
- Operate drill motor between 400-600 RPMs higher speeds will damage bit, reducing the number of holes the bit can effectively drill
- First, drill a small hole with a 5/32" PORC+ bit and then use a larger bit depending on hole required (3/16", 1/4", 5/16", 3/8", 1/2")
- Use some pressure during drilling; however, too much pressure can make the bit move and cause the hole not to be centered as marked and could also cause the tile to break
- To extend the life of the bit, let it cool down for several minutes between each hole

Sizes	ITEM NO. Carded	ITEM NO. Bulk	DIAMETER	FLUTE Length	OVERALL Length	SHANK
	01425*	01416	5/32"	1-1/2"	3-1/8"	Straight
	01430*	01418	3/16"	1-7/8"	3-1/2"	Straight
	01435*	01420	1/4"	2-3/8"	4-1/8"	Straight
	01440*	01422	5/16"	2-3/8"	4-1/2"	Straight
	01445*	01424	3/8"	3-1/8"	5-5/16"	Straight
		01426	1/2"	3-5/8"	6-1/4"	3/8"
		WO 05				
set	ITEM Number	NO. OF Pieces	DESCRIPTION			

^{01405 4 5/32&}quot;, 5/32", 5/32", 3/16", 1/4"

* Carded bits include 5/32" pilot bit

ALSO AVAILABLE FROM ARTU



ARTU-USA, Inc.
330 Fields Drive
Aberdeen, NC 28315
P: (800) 367-2788
F: (910) 944-1884
sales@artu.com
@2016 ARTU USA



