

# PC 610



## PERFORMANCE GRADE CLOTH ABATEMENT DUCT TAPE

### TYPICAL APPLICATIONS

- For sealing walls, doors and windows in abatement applications
- Ideal for use on rugged jobs in warm and cold climates, as well as in dry and wet environments

### PRODUCT FEATURES

- Excellent cold temperature adhesion
- Superior holding power to poly-sheeting, metal and unpainted wood
- Easy to unwind and tear
- Will not twist or curl during application

### CONSTRUCTION

Overall Grade/Function: Performance

Backing: Polyethylene film with a cloth carrier

Adhesive: Blended rubber

### STANDARD WIDTH(S)

48 mm    72 mm

### STANDARD LENGTH(S)

55 m

Contact your Shurtape sales representative for other available sizes

### STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

### COLOR(S)



PHYSICAL PROPERTIES	STANDARD	METRIC
Tensile Strength	26 lbs/in width	45.5 N/10 mm
Adhesion to Stainless Steel	56 oz/in width	6.13 N/10 mm
Thickness	10 mils	0.25 mm
Elongation	23%	23%
Service Temperature Range	25 F to 200 F	-4 C to 93 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

