



# PROFESSIONAL TRAFFIC STRIPING PAINT

## DESCRIPTION AND USES

Rust-Oleum® Professional Traffic Striping Paint is a single-component, water based acrylic coating. Dries fast (in 30 minutes), and can accept traffic after 8 hours. Use for large striping jobs on interior or exterior concrete or asphalt surfaces such as large commercial parking lots, curbs, or aisles.

## PRODUCTS

SKU	DESCRIPTION (Flat 1-Gallon)
2526402	Blue
2548402	Yellow
2593402	White

## PRODUCT APPLICATION

### SURFACE PREPARATION

ALL SURFACES: Remove all dirt, grease, oil, salt and chemical contaminants by washing the surface with a detergent or other suitable cleaner. Rinse thoroughly with fresh water and allow to fully dry.

**WARNING!** If you scrape, sand, or remove old paint, you may release lead dust. LEAD IS TOXIC. EXPOSURE TO LEAD DUST CAN CAUSE SERIOUS ILLNESS SUCH AS BRAIN DAMAGE, ESPECIALLY IN CHILDREN. PREGNANT WOMEN SHOULD ALSO AVOID EXPOSURE. Wear a NIOSH-approved respirator to control lead exposure. Clean up carefully with a HEPA vacuum and a wet mop. Before you start, find out how to protect yourself and your family by contacting the National Lead Information Hotline at 1-800-424-LEAD or log on to [www.epa.gov/lead](http://www.epa.gov/lead).

## PRODUCT APPLICATION (cont.)

### APPLICATION

Apply only when the air and surface temperatures are between 50-90°F (10-32°C) and the relative humidity is below 85%. The surface temperature should be at least 5°F (3°C) above the dew point. Protect from rain for 24 hours.

### EQUIPMENT RECOMMENDATIONS

**BRUSH:** For quick touch-ups and small areas such as parking curbs.

**ROLLER:** Use a good quality, ¾ inch nap roller the appropriate width for the stripe required.

**STRIPING MACHINE:** Apply by bulk striping machine. The Rust-Oleum Striping Machine (product #2395000) is not compatible.

### THINNING

Thinning is not recommended. If necessary to ease brushing or rolling, up to 5% water may be added.

### CLEAN-UP

Soap and water.

	<b>TECHNICAL DATA</b>	<b>PRO-07</b>
	<b>PROFESSIONAL TRAFFIC STRIPING PAINT</b>	

**PHYSICAL PROPERTIES**

		TRAFFIC STRIPING PAINT
<b>Resin Type</b>		Acrylic
<b>Pigment Type</b>		Varies with color
<b>Solvents</b>		Methanol, Water
<b>Weight</b>	<b>Per Gallon</b>	12.4-12.7 lbs.
	<b>Per Liter</b>	1.49-1.52 kg
<b>Solids</b>	<b>By Weight</b>	67.7-69.1%
	<b>By Volume</b>	50.6-51.6%
<b>Volatile Organic Compounds</b>		<100 g/l (0.83 lbs./gal.)
<b>Theoretical Coverage at 1 mil DFT (25µ)</b>		675-690 sq. ft./gal. (16.6-17.0 m <sup>2</sup> /l)
<b>Practical Coverage at Recommended DFT (assumes 15% material loss)</b>		4 inch stripe (10.2 cm) – 460 linear ft./gal. (37.1 m/l) (coverage is dependent on surface porosity)
<b>Dry Times at 70-80°F (21-27°C) and 50% Relative Humidity</b>	<b>Touch</b>	30 minutes
	<b>Recoat</b>	After 4 hours
	<b>Traffic</b>	After 8 hours
<b>Shelf Life</b>		5 years (protect from freezing)
<b>Flash Point</b>		>200°F (93°C)
<b>Safety Information</b>		For additional information, see SDS

Calculated values are shown and may vary from the actual manufactured material.

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.