



20 AMP POWER CONTROL RELAY

RIBT242B

Enclosed Relays Hi/Low Separation 20 Amp
2 SPDT with 24 Vac/dc Coil



SPECIFICATIONS

- | | | | |
|--|--|--|--|
| <p># Relays & Contact Type: Two (2) SPDT Continuous Duty Coil</p> <p>Expected Relay Life: 10 million cycles minimum mechanical</p> <p>Operating Temperature: -30 to 140° F</p> <p>Humidity Range: 5 to 95% (noncondensing)</p> <p>Operate Time: 18ms</p> <p>Relay Status: LED On = Activated</p> <p>Dimensions: 4.00" x 4.00" x 1.80" with .50" NPT Nipple</p> <p>Wires: 16", 600V Rated</p> <p>Approvals: UL Listed, UL916, UL864, C-UL
California State Fire Marshal, CE, RoHS</p> <p>Housing Rating: UL Accepted for Use in Plenum, NEMA 1</p> <p>Gold Flash: No</p> <p>Override Switch: No</p> | <p>Contact Ratings:</p> <ul style="list-style-type: none"> 20 Amp Resistive @ 277 Vac 5 Amp Resistive @ 480 Vac 20 Amp Ballast @ 277 Vac 16 Amp Electronic Ballast @ 277 Vac (N/O) 10 Amp Tungsten @ 120 Vac (N/O) 770 VA Pilot Duty @ 120 Vac 1,110 VA Pilot Duty @ 277 Vac 2 HP @ 277 Vac 1 HP @ 120 Vac | <p>Coil Current:</p> <ul style="list-style-type: none"> 50 mA @ 18 Vac 83 mA @ 24 Vac 33 mA @ 22 Vdc 35 mA @ 24 Vdc 47 mA @ 30 Vdc | <p>Coil Voltage Input:</p> <ul style="list-style-type: none"> 24 Vac/dc; 50-60 Hz Drop Out = 2.1 Vac / 3.8 Vdc Pull In = 18 Vac / 22 Vdc |
|--|--|--|--|