



# SAFETY DATA SHEET

US OSHA Hazard Communication Standard (29 CFR 1910.1200) and Canada WHMIS 2015 which includes the amended Hazardous Products Act (HPA) and the Hazardous Products Regulation (HPR)

Issuing Date 18-Dec-2022

Revision Date 19-Jan-2024

Revision Number 3

## 1. Identification

### Product identifier

**Product Name** Di-Ester Synthetic Reciprocating Compressor Oil - ISO 100

### Other means of identification

**Product Code(s)** OIL004

**Synonyms** None

### Recommended use of the chemical and restrictions on use

**Recommended use** Compressor oil

**Restrictions on use** Avoid formation of mists

### Details of the supplier of the safety data sheet

#### Manufactured for

Airbase Industries  
1000 Cass Drive  
Englewood, OH 45315  
T: 877-283-7614

### Emergency telephone number

**Emergency telephone** CHEMTREC: Within USA and Canada: 1-800-424-9300  
Outside the USA and Canada: +1 703-741-5970  
(collect calls accepted) 24/7

## 2. Hazard(s) identification

### Classification

Reproductive toxicity	Category 2
-----------------------	------------

### Label elements

#### Warning

#### Hazard statements

Suspected of damaging fertility or the unborn child.



**Precautionary Statements - Prevention**

Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Wear protective gloves, protective clothing, eye protection and face protection.

**Precautionary Statements - Response**

IF exposed or concerned: Get medical advice/attention.

**Precautionary Statements - Storage**

Store locked up.

**Precautionary Statements - Disposal**

Dispose of contents and container to an approved waste disposal plant.

**Other information**

No information available.

**3. Composition/information on ingredients****Substance**

Not applicable.

**Mixture**

Chemical name	CAS No	Weight-%	Hazardous Material Information Review Act registry number (HMIRA registry #)	Date HMIRA filed and date exemption granted (if applicable)
Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene	68411-46-1	0.1-1	-	-

**Chemical Additions**

The classification as a carcinogen does not apply as it can be shown that the substance(s) contain(s) less than 3% DMSO extract as measured by IP 346.

**4. First-aid measures****Description of first aid measures**

<b>General advice</b>	Show this safety data sheet to the doctor in attendance.
<b>Inhalation</b>	Remove person to fresh air and keep comfortable for breathing.
<b>Eye contact</b>	Rinse thoroughly with plenty of water, also under the eyelids. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention if irritation develops and persists.
<b>Skin contact</b>	Wash skin with soap and water. Take off contaminated clothing. Get medical attention if irritation develops and persists.
<b>Ingestion</b>	Rinse mouth. Do NOT induce vomiting. Never give anything by mouth to an unconscious person.
<b>Self-protection of the first aider</b>	Wear personal protective clothing (see section 8).

**Most important symptoms and effects, both acute and delayed**

<b>Symptoms</b>	May cause gastrointestinal discomfort if consumed in large amounts. May cause temporary eye irritation. Repeated or prolonged skin contact may cause skin irritation and/or dermatitis and sensitization in susceptible persons. Symptoms of overexposure are dizziness, headache, tiredness, nausea, unconsciousness and difficulty breathing.
-----------------	---

**Indication of any immediate medical attention and special treatment needed**

**Note to physicians** Treat symptomatically.

**5. Fire-fighting measures**

**Suitable Extinguishing Media** Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam. Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable extinguishing media** Do not use a solid water stream as it may scatter and spread fire.

**Specific hazards arising from the chemical** Containers can burst or explode when heated, due to excessive pressure build-up. Thermal decomposition can lead to release of irritating gases and vapors.

**Hazardous combustion products** Carbon monoxide, carbon dioxide and unburned hydrocarbons (smoke).

**Explosion data**

**Sensitivity to mechanical impact** None.

**Sensitivity to static discharge** None.

**Special protective equipment and precautions for fire-fighters** Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.

**6. Accidental release measures****Personal precautions, protective equipment and emergency procedures**

**Personal precautions** Use personal protective equipment as required. See section 8 for more information. Ensure adequate ventilation.

**For emergency responders** Use personal protection recommended in Section 8.

**Methods and material for containment and cleaning up**

**Methods for containment** Prevent further leakage or spillage if safe to do so.

**Methods for cleaning up** Contain and collect spillage with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see Section 13). Clean contaminated surface thoroughly. After cleaning, flush away traces with water.

**Reference to other sections** For additional information see: Section 8: Exposure controls/personal protection; Section 12: Ecological information; Section 13: Disposal considerations.

**7. Handling and storage****Precautions for safe handling**

**Advice on safe handling** Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Do not eat, drink or smoke when using this product. Remove contaminated clothing and shoes. Wash hands thoroughly after handling.

**Conditions for safe storage, including any incompatibilities**

**Storage Conditions** Keep containers tightly closed in a dry, cool and well-ventilated place. Store locked up. Do not reuse empty containers. Keep away from Incompatible materials. See section 10 for more information. Store in accordance with local regulations.

**8. Exposure controls/personal protection****Control parameters**

**Exposure Limits** Under conditions which may generate mists, the following exposure limits are recommended: Long-term exposure limit (8-hour TWA): 5 mg/m<sup>3</sup>. Short-term exposure limit (15-minute): 10 mg/m<sup>3</sup>.

**Biological occupational exposure limits** This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies.

### Appropriate engineering controls

**Engineering controls** Ensure adequate ventilation, especially in confined areas.

### Individual protection measures, such as personal protective equipment

**Eye/face protection** If there is a risk of contact: Wear safety glasses with side shields (or goggles).

**Hand protection** If there is a risk of contact: Wear suitable gloves. Ensure that the breakthrough time of the glove material is not exceeded. Refer to glove supplier for information on breakthrough time for specific gloves.

**Skin and body protection** If there is a risk of contact: Wear suitable protective clothing.

**Respiratory protection** No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

**Environmental exposure controls** Avoid release to the environment.

**General hygiene considerations** Do not eat, drink or smoke when using this product. Wash hands before breaks and immediately after handling the product.

## 9. Physical and chemical properties

### Information on basic physical and chemical properties

#### Appearance

Physical state	Liquid
Color	Amber
Odor	Mild hydrocarbon
Odor threshold	No information available

#### Property

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH		No data available
Melting point / freezing point		No data available
Initial boiling point and boiling range		No data available
Flash point	250 - 264 °C / - 507.2 °F	Cleveland Open Cup ASTM D 92
Evaporation rate		No data available
Flammability		No data available
Flammability Limit in Air		
Upper flammability or explosive limits		No data available
Lower flammability or explosive limits		No data available
Vapor pressure		No data available
Vapor density		No data available
Relative density	0.911-0.9141	No data available
Water solubility		No data available
Solubility(ies)		No data available
Partition coefficient		No data available
Autoignition temperature		No data available
Decomposition temperature		No data available

<b>Kinematic viscosity</b>	67.7-150.4 cSt at 40 °C 10.3-17.7 cSt at 100 °C	ASTM D445
<b>Dynamic viscosity</b>		No data available
<b>Other information</b>		
<b>Explosive properties</b>	No information available.	
<b>Oxidizing properties</b>	No information available.	
<b>Softening point</b>	No information available	
<b>Pour Point</b>	-45 - (-38)°C [ASTM D 97]	
<b>Fire Point</b>	270-280°C (COC) [ASTM D 92]	
<b>Molecular weight</b>	No information available	
<b>VOC content</b>	No information available	
<b>Liquid Density</b>	No information available	
<b>Bulk density</b>	No information available	

## 10. Stability and reactivity

<b>Reactivity</b>	None under normal use conditions.
<b>Chemical stability</b>	Stable under normal conditions.
<b>Possibility of hazardous reactions</b>	None under normal processing.
<b>Conditions to avoid</b>	None known based on information supplied.
<b>Incompatible materials</b>	None known based on information supplied.
<b>Hazardous decomposition products</b>	Thermal decomposition can lead to release of irritating gases and vapors. Carbon monoxide, carbon dioxide and unburned hydrocarbons (smoke).

## 11. Toxicological information

### Information on likely routes of exposure

#### Product Information

<b>Inhalation</b>	Specific test data for the substance or mixture is not available.
<b>Eye contact</b>	Specific test data for the substance or mixture is not available.
<b>Skin contact</b>	Specific test data for the substance or mixture is not available.
<b>Ingestion</b>	Specific test data for the substance or mixture is not available.

### Symptoms related to the physical, chemical and toxicological characteristics

<b>Symptoms</b>	May cause temporary eye irritation. Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea. Repeated or prolonged skin contact may cause skin irritation and/or dermatitis and sensitization in susceptible persons. Symptoms of overexposure are dizziness, headache, tiredness, nausea, unconsciousness and difficulty breathing.
-----------------	---

### Acute toxicity

#### Numerical measures of toxicity

#### Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene	> 5000 mg/kg ( Rat )	> 2000 mg/kg (Rat)	-

**Delayed and immediate effects as well as chronic effects from short and long-term exposure****Skin corrosion/irritation** No information available.

Component Information	
Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene (68411-46-1)	
Method	OECD Test No. 404: Acute Dermal Irritation/Corrosion
Species	Rabbit
Exposure route	Dermal
Effective dose	0.5 mL
Exposure time	4 hours
Results	Mild skin irritant

**Serious eye damage/eye irritation** No information available.

Component Information	
Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene (68411-46-1)	
Method	OECD Test No. 405: Acute Eye Irritation/Corrosion
Species	Rabbit
Exposure route	Eye
Effective dose	0.1 mL
Results	non-irritant

**Respiratory or skin sensitization** No information available.**Germ cell mutagenicity** No information available.**Carcinogenicity** The supplier declares that it can be shown that the substance(s) contain less than 3% DMSO extract as measured by IP 346.**Reproductive toxicity** Contains a known or suspected reproductive toxin. Classification based on data available for ingredients. Suspected of damaging fertility or the unborn child.**STOT - single exposure** No information available.**STOT - repeated exposure** No information available.**Aspiration hazard** Due to the viscosity, this product does not present an aspiration hazard.**12. Ecological information****Ecotoxicity** Large or frequent spills may have hazardous effects on the environment.

Chemical name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene 68411-46-1	EC50: 51mg/L (48h, Daphnia magna)	LC50: >100mg/L (96h, Danio rerio)	-	-

**Persistence and degradability** No information available.**Bioaccumulation****Component Information**

Chemical name	Partition coefficient
Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene	6.66

68411-46-1

**Mobility in soil** No information available.**Other adverse effects** No information available.**13. Disposal considerations****Waste treatment methods****Waste from residues/unused products** Dispose of in accordance with local regulations, Dispose of waste in accordance with environmental legislation.**Contaminated packaging** Do not reuse empty containers.**14. Transport information****DOT** Not regulated**TDG** Not regulated**IATA** Not regulated**IMDG** Not regulated**15. Regulatory information****Safety, health and environmental regulations/legislation specific for the substance or mixture****International Regulations****The Montreal Protocol on Substances that Deplete the Ozone Layer** Not applicable**The Stockholm Convention on Persistent Organic Pollutants** Not applicable**The Rotterdam Convention** Not applicable**International Inventories**

Contact supplier for inventory compliance status

Chemical name	CAS No	US TSCA Inventory listing	US TSCA inactive/active designation
Bis(tridecyl) adipate	16958-92-2	Present	Active
Polyisobutylene	9003-27-4	Present	Active
non hazardous ingredient	-		
1,2-Dihydro-2,2,4-trimethylquinoline, oligomers	26780-96-1	Present	Active
Dibutyl [(dipropoxyphosphinothioyl)thio]succinate	68413-47-8	Present	Active
Benzenamine, N-phenyl-, reaction products with 2,4,4-trimethylpentene	68411-46-1	Present	Active
Trade secret	Proprietary	Present	Active
Polysulfides, di-tert-dodecyl	68425-15-0	Present	Active
Hydrogenated base oil	64742-70-7	Present	Active
Dihydro-3-(tetrapropenyl)furan-2,5-dione	26544-38-7	Present	Active
Hydrogenated base oil	64742-46-7	Present	Active
(Z)-N-methyl-N-(1-oxo-9-octadecenyl)glycine	110-25-8	Present	Active
1H-Benzotriazole-1-methanamine,	94270-86-7	Present	Active

N,N-bis(2-ethylhexyl)- 2,5-bis(octylidithio)-1,3,4-thiadiazole	13539-13-4	Present	Active
Diphenylamine	122-39-4	Present	Active
2,6-Di-tert-butyl-p-cresol	128-37-0	Present	Active
Xylene	1330-20-7	Present	Active
Ethylbenzene	100-41-4	Present	Active
Benzene	71-43-2	Present	Active
Naphthalene	91-20-3	Present	Active

\*Contact supplier for details. One or more substances in this product are either not listed on the US TSCA inventory, listed on the confidential US TSCA inventory or are otherwise exempted from inventory listing requirements

### US Federal Regulations

#### **SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.

#### **SARA 311/312 Hazard Categories**

Should this product meet EPCRA 311/312 Tier reporting criteria at 40 CFR 370, refer to Section 2 of this SDS for appropriate classifications.

#### **CWA (Clean Water Act)**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

#### **CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

### US State Regulations

#### **California Proposition 65**

This product contains the following Proposition 65 chemicals:

Chemical name	California Proposition 65
Ethylbenzene - 100-41-4	Carcinogen
Benzene - 71-43-2	Carcinogen Developmental Male Reproductive
Naphthalene - 91-20-3	Carcinogen

### U.S. State Right-to-Know Regulations

Chemical name	New Jersey	Massachusetts	Pennsylvania
Hydrogenated base oil 64742-70-7	-	X	-
Diphenylamine 122-39-4	X	X	X
2,6-Di-tert-butyl-p-cresol 128-37-0	X	X	X
Xylene 1330-20-7	X	X	X
Ethylbenzene	X	X	X

100-41-4			
Benzene 71-43-2	X	X	X
Naphthalene 91-20-3	X	X	X

**U.S. EPA Label Information**

EPA Pesticide Registration Number Not applicable

**Key or legend to abbreviations and acronyms used in the safety data sheet****Legend Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION**

TWA	TWA (time-weighted average)	STEL	STEL (Short Term Exposure Limit)
Ceiling	Maximum limit value	*	Skin designation

**Key literature references and sources for data used to compile the SDS**

U.S. Environmental Protection Agency ChemView Database  
 European Food Safety Authority (EFSA)  
 EPA (Environmental Protection Agency)  
 Acute Exposure Guideline Level(s) (AEGL(s))  
 U.S. Environmental Protection Agency Federal Insecticide, Fungicide, and Rodenticide Act  
 U.S. Environmental Protection Agency High Production Volume Chemicals  
 Food Research Journal  
 Hazardous Substance Database  
 International Uniform Chemical Information Database (IUCLID)  
 Japan GHS Classification  
 Australia National Industrial Chemicals Notification and Assessment Scheme (NICNAS)  
 NIOSH (National Institute for Occupational Safety and Health)  
 National Library of Medicine's ChemID Plus (NLM CIP)  
 National Toxicology Program (NTP)  
 New Zealand's Chemical Classification and Information Database (CCID)  
 Organization for Economic Co-operation and Development Environment, Health, and Safety Publications  
 Organization for Economic Co-operation and Development High Production Volume Chemicals Program  
 Organization for Economic Co-operation and Development Screening Information Data Set  
 World Health Organization

Issuing Date 18-Dec-2022

Revision Date 19-Jan-2024

Revision Note Customer-Specific SDS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

**End of Safety Data Sheet**