

kathy ireland®
HOME

by

LUMINANCEBRANDS™



A. Shown in Oil Rubbed Bronze with Dark Cherry Blades

52" Snugger CF805S

MODEL FEATURES

- 52" Blade Span
- 5 Reversible Blades
- Light Fixture Adaptable
- 3-Speed Pull Chain Operation
- Flush Mount



LED LIGHT
FIXTURE
ADAPTABLE



SHIPS TO
CANADA



LIMITED
LIFETIME
MOTOR
WARRANTY

PERFORMANCE SPECIFICATIONS

Speed	Airflow	Electricity Use	Airflow Efficiency	RPM
	Cubic Ft. Per Min.	Watts (Excl. Lights)	Cubic Ft. Per Min. Per Watt	Revolutions per Minute
High	3485	64	55	170
Low	1275	10	127	65

Blade Pitch	Accepts 2.5" DR	Amps	LED Specifications			
			Lumens	Watts	CRI	CCT (K)
12°	N	0.6	N/A	N/A	N/A	N/A

Control Included	Receiver Included	Manual/Remote Reverse Switch	Dimming Light	Downrod Length	Motor Lead Lengths
3-Speed Pull Chain	N	Manual	N/A	N/A	N/A

ENERGYGUIDE INFORMATION

ENERGYGUIDE

Estimated
Yearly Energy Cost

\$11

Cost Range of Similar Models (19" – 84")

\$3

▼

\$34

• Based on 12 cents per kWh and 6.4 hours use per day
• Your cost depends on rates and use
• Energy Use: 39 Watts

Airflow

2,449

Cubic Feet Per Minute

• The higher the airflow, the more air the fan will move
• Airflow Efficiency: 64 Cubic Feet Per Minute Per Watt

All estimates based on typical use, excluding lights ftc.gov/energy

Energy information listed above is a weighted average of High and Low speeds.

52" SNUGGER



B. Shown in Appliance White with Appliance White Blades



C. Shown in Brushed Steel with Dark Cherry Blades and Low Profile Light Fixture (LK53BS)


A. **52" SNUGGER – OIL RUBBED BRONZE**
CF805SORB - Dark Cherry/Medium Oak Blades

B. **52" SNUGGER – APPLIANCE WHITE**
CF805SWW - Appliance White/Bleached Oak Blades

C. **52" SNUGGER – BRUSHED STEEL**
CF805SBS - Dark Cherry/Mahogany Blades

SHIPPING SPECIFICATIONS: Carton Weight: **16.00 LBS** | Length: **19.50"** | Width: **12.25"** | Depth: **7.75"**

Product Dimensions



- A. Total Fan Height: **7.3"**
- B. Bottom of Blade to Ceiling: **7.6"**
- C. Width of Housing: **11.0"**
- D. Width of Canopy: **N/A**
- Motor Size (mm): **153 x 15**
- Product Weight: **13.9 LBS**

Optional Controls



SW46
4-Speed
Slide Control



SW90
Fan & Light Dual
Slide Control

Recommended Accessories

Sold Separately



LED Light Fixtures