

LIGHTWEIGHT KNUCKLE-COATED LATEX GLOVE WITH HIGH CUT PROTECTION

Durable high cut resistance grip glove with thermal resistance up to 250°C/484°F for short contact. Outstanding grip in wet and dry handling conditions.

FEATURES

- › Cut resistance: level F / ANSI A6
- › Lightweight and durable 13g liner made of para-aramid and steel fibre to protect against high cut risks
- › Crinkle latex knuckle coating offers optimum wet and dry grip
- › Contact heat protection up to 250°C / 482°F for a short period (15 sec max)
- › Designed for easy movement and continuous wear
- › Seamless knit prevents irritation
- › Elasticated wrist provides a secure fit



SUITABLE FOR


Typical Industries

- Public utilities
- Automotive
- Construction
- Glass
- Steel and Metals
- Waste management

Suitable Applications

- Glass Handling
- Metal Fabrication
- Hazardous Recycling
- Paper Manufacturing
- Plastics Manufacturing
- Waste handling

CERTIFICATION



See overleaf for explanation

PRODUCTION INFORMATION

MATERIALS	LINER:	13 gauge para-aramid, steel fibre
	COATING:	Latex
COLOUR	Yellow/Blue	
LENGTH (mm)	250 (size dependent)	
CUFF STYLE	Elasticated knit wrist	

ORDERING DETAILS

SIZE	CODE	PACKAGING
6/XS	SKG00107BB	Each pair single packed, 6 pairs in a polybag 120 pairs per case
7/S	SKG00107BD	
8/M	SKG00107BF	
9/L	SKG00107BH	
10/XL	SKG00107BJ	
11/XXL	SKG00107BL	
12/XXXL	SKG00107BN	


RECOMMENDATIONS FOR USE

- **USE:** General handling glove with cut protection. Not suitable for high thermal (beyond 250°C / 482°F), electrical and chemical protection. Do not use near moving machines if there is a risk of entanglement
- **STORAGE:** Store in dry conditions in the original packaging and away from direct sunlight
- **CLEANING:** To clean, wipe with a damp cloth. Note: The performance characteristics of worn and laundered gloves may differ from the results shown. Inspect the gloves to ensure no damage is present.
- **LIFETIME:** Service life depends on the glove application and therefore cannot be specified. It is the responsibility of user to ensure the glove is suitable for its intended use
- **WARNING:** Latex may cause allergies

CERTIFICATION LEGENDS



MECHANICAL HAZARDS EN 388:2016 PERFORMANCE LEVELS*



*If tests are not performed or are not applicable, 'X' will be placed instead of a number/letter



HEAT AND FIRE EN 407

PERFORMANCE LEVELS



CLASSIFICATION FOR CUT RESISTANCE	
Measured breakthrough time	Permeation performance index (grams)
A1	≥ 200
A2	≥ 500
A3	≥ 1000
A4	≥ 1500
A5	≥ 2200
A6	≥ 3000
A7	≥ 4000
A8	≥ 5000
A9	> 6000

ANSI/ISEA 105-2016 ABRASION RATING CHART							
Abrasion Level Rating	0	1	2	3	4	5	6
Gram Load	500	500	500	500	1000	1000	1000
Abrasion Cycles to Fail	<100	≥100	≥500	≥1,000	≥3,000	≥10,000	≥20,000

ANSI/ISEA PUNCTURE RESISTANCE	
ANSI Puncture Level	Puncture Resistance (newtons)
1	10-19
2	20-59
3	60-99
4	100-149
5	150+

Puncture Resistance (ANSI/ISEA 105): Puncture resistance is determined by the max force that it takes, exerted from a probe, to puncture the fabric.