



Main

Range	TeSys
Device short name	VLS1P
Product or component type	Additional pole
Performance level	High performance
Poles description	1P
Contacts type and composition	1 NO
Contact operation	Simultaneous
Range compatibility	TeSys VARIO LS VLS3P
Network type	AC
Network frequency	50/60 Hz
Suitability for isolation	Yes

Complementary

Mounting location	Left Right
Mounting support	DIN rail
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ith] conventional free air thermal current	63 A 131 °F (55 °C)
[Ithe] conventional enclosed thermal current	45 A
[Ie] rated operational current	60 A Ue: 600 V UL 508 63 A AC-21A Ue: 400 V 63 A AC-21A Ue: 500 V 63 A AC-21A Ue: 690 V 45 A AC-22A Ue: 400 V 45 A AC-22A Ue: 500 V 45 A AC-22A Ue: 690 V 45 A AC-23A Ue: 400 V 25 A AC-23A Ue: 500 V 25 A AC-23A Ue: 690 V
Rated operational power in W	22 KW 400 V AC-23A) 22 KW 500 V AC-23A) 22 kW 690 V AC-23A)
Intermittent duty class	Class 120 - 60 %
Making capacity (I Rms)	120 A 690 V AC-22A 400 A 690 V AC-23A 94.5 A 690 V AC-21A
[Icm] rated short-circuit making capacity	1128 A 690 V
[Icw] rated short-time withstand Rms current	800 A 690 V 1 s
Rated conditional short-circuit current	50 kA 400 V 63 A gG
Breaking capacity	120 A 690 V AC-22A) 320 A 690 V AC-23A) 94.5 A 690 V AC-21A)
Mechanical durability	100000 cycles
Electrical durability	15000 cycles AC-21
Connections - terminals	Power circuit screw clamp terminals 0.02 in ² (10 mm ²) solid Power circuit screw clamp terminals 0.02 in ² (16 mm ²) flexible - without cable end
Tightening torque	Power circuit 15.93...17.70 lbf.in (1.8...2 N.m) screw clamp terminals
Height	3.07 in (78 mm)
Width	0.47 in (12 mm)
Depth	1.72 in (43.6 mm)

Net Weight	0.09 lb(US) (0.04 kg)
Color	Gray

Environment

Standards	UL 508 CSA C22.2 No 14 IEC 60947-3
Product certifications	CULus GL
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 2...100 Hz Fc 0.7 g) IEC 60068-2-6 Shocks 11 ms Ea 15 gn) IEC 60068-2-27
Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Fire resistance	1760 °F (960 °C) IEC 60695-2-11

Ordering and shipping details

Category	21734 - TESYS VLS DISCONNECT SWITCHES
Discount Schedule	CP1
GTIN	00785901566311
Nbr. of units in pkg.	1
Package weight(Lbs)	0.1 lb(US) (0.05 kg)
Returnability	Yes
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.07 in (7.8 cm)
Package 1 width	0.47 in (1.2 cm)
Package 1 Length	1.72 in (4.36 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.