

SPECIFICATION SHEET

RF1-B - Reflex

Anti-Fatigue Light Duty Tile TPE

- Compression dome surface ensures optimal ergonomic anti-fatigue support particularly for low motion workers with lighter footwear
- Excellent for any light duty work environment
- Configures easily to any workspace size
- Interlocking tabs ensure a strong connection
- Easy to clean and maintain
- 64 leg support structure underneath provides weight load dispersion and channels for cord control
- Can be edged with A3, A4, A5 and A6 edges or corners



DIMENSIONS	18 in x 18 in x 1 in
WEIGHT	4.5 lbs
COMPOSITION	Recycled TPE
TENSILE STRENGTH (ASTM D412)	Stress: 1413 PSI Strain: 689 %
DUROMETER	Shore hardness "A" 75 (+/-5)
FRICITION (ASTM D1894)	Static: 1.18 Dynamic: 0.76
WARRANTY	Lifetime warranty against manufacturer's defects
COLORS	Black

ANTI-FATIGUE



ANTI-SLIP



RECYCLED





WORKS AS HARD AS YOU DO



**WE DIVERT
2M LBS
OF PVC FROM
LANDFILLS
ANNUALLY**

1-877-578-0101

info@safe-flex.com

www.safe-flex.com



Premium. Flexible. Safe.

The Safe-Flex Floor System is a premium, flexible and safe modular industrial flooring solution that solves challenges faced by many organizations.

The patented Compression Flex construction provides the industry's top anti-fatigue support. The floor system can be custom fit or purchased in ready-made standard kits. The anti-slip varieties work in wet or even oily environments, and bevelled edges ensure that workplace slips, trips and falls are greatly reduced. The ESD and anti-microbial options provide additional environmental control. All matting options are impervious to most chemicals and are class 1 fire resistant. Tiles are sustainably produced using recycled materials and feature world class connection lugs that will last beyond the competition's. A Safe-Flex Floor System works as hard as you do to protect your most important asset—your employees.

AN  **ergoadvantage inc** BRAND