3M

Scotch-Weld™ Hi-Strength Postforming 94 CA Spray Adhesive

Technical Data November 2017

Product Description A low VOC, high performance, postformable grade spray adhesive with a unique low telegraphing pebble spray pattern.

Key Features

- Bonds to a variety of demanding substrates like decorative laminate, metal, and some rubbers
- Typically used in woodworking and specialty vehicle applications, especially where VOC's are a concern.
- · Formulated with exceptionally high solids.
- · Features a low telegraphing spray pattern.

Typical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Product	3M™ Scotch-Weld™ Hi-Strength	3M™ Scotch-Weld™ Hi-Strength	
	Postforming 94 CA	Postforming 94 CA Spray	
	Cylinder Spray Adhesive	Adhesive	
Base:	Synthetic Elastomer	Synthetic Elastomer	
Solids Content - (by wt.):	28%	34%	
Density (lbs/gal):	7.9	7.8	
Viscosity (cps):	N/A	< 500	
Color(s):	Translucent and Red	Translucent and Red	
Volatile Organic Compounds (VOC):	< 80 g/L	< 80 g/L	
Hazardous Air Pollutants (HAPS) %	No	No	
wt (calculated):			
CARB Compliant:	N/A	N/A	
SCAQMD 1168 Compliant:	Yes	Yes	
GREENGUARD Indoor Air Quality	Yes	Yes	
Certified®:			
LEED® Eligible:	Yes	Yes	
Coverage @ 2.5 gms /ft² per lb	51 62		
(sqft):			
Spray Pattern:	Pebble	Pebble or Lace	
Dry Time:	1 minute	1 minute	
Bonding Range:	1 – 15 minutes	1 – 15 minutes	
Shear Adhesion Failure Test -	210F	210F	
SAFT ⁽¹⁾ :			
Flammable Solvent:	Yes	Yes	
Flammable Propellant:	Yes	N/A	

[®]SAFT Shear Adhesion Failure Test with birch plywood, 1 inch overlap, 100 grams used, temperature start at 90F and ramped 10F every 10 mn. until complete failure.

Available Sizes - Note: 94 CA FF = 3M[™] Scotch-Weld[™] Hi-Strength Postforming 94 CA Spray Adhesive (94 CA) but with NO ADDED FRAGRANCE

	3M Stock Number	3M Stock Number	3M Stock Number	3M Stock Number
Container Size	94 CA - clear	94 CA - red	94 CA FF - clear	94 CA FF - red
Mini Cylinder – 7.6 lbs.	62-4960-8010-2	62-4970-8010-1	62-4920-8010-6	N/A
Large Cylinder – 26.2 lbs.	62-4960-8030-0	62-4970-8030-9	62-4920-8030-4	62-4940-8030-2
Interm. Cyl. – 128 lbs.	62-4960-8150-6	62-4970-8150-5	62-4920-8150-0	62-4940-8150-8
Jumbo Cyl. – 266 lbs.	62-4960-8300-7	62-4970-8300-6	62-4920-8300-1	62-4940-8300-9
5 gallon pail – 40 lbs.	62-4924-8530-5	62-4988-8530-0	62-4922-8530-9	62-4944-8530-3
54 gallon drum – 432 lbs.	62-4924-9530-4	62-4988-9530-9	62-4922-9530-8	62-4944-9530-2
Open Head drum	62-4924-9531-2	62-4988-9531-7	N/A	N/A

3M[™] Scotch-Weld[™] Hi-Strength Postforming 94 CA Spray Adhesive

Store product at 60°-80°F (16°-27°C) for maximum storage life. Higher temperatures reduce normal storage life. Lower temperatures may cause increased viscosity of a temporary nature. Rotate stock on a "first in-first out" basis.			
When stored at the recommended conditions in original, unopened container, this product has a shelf life if 15 months from date of shipment.			
Refer to product label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.			
The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, cndompleteness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license unde any 3M or third party intellectual property rights is granted or implied with this information.			
Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.			
Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.			
Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.			

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M

Industrial Adhesives and Tapes Division 3M Center, Building 225-3S-06 St. Paul, MN 55144-1000 800-362-3550 • 877-369-2923 (Fax) www.3M.com/sprayadhesives 3M and Scotch-Weld are trademarks of 3M Company. The GREENGUARD INDOOR AIR QUALITY CERTIFIED Mark is a registered certification mark owned by Air Quality Sciences, Inc. and used under license through the Greenguard Environmental Institute. LEED® is a registered trademark of the United States Green Building Council (USGBC). ©3M 2017