

Product data sheet

Characteristics

8536SAG12V02CS

NEMA Motor Starter, Type S, nonreversing, Size 00, 9A, 2 HP at 460 VAC, 5 kA SCCR, 3 phase, 3 pole, melting alloy, 120 VAC coil, NEMA 1



Main

Product Type	Motor starter
Product Range	S
Starter Type	Non reversing

Complementary

NEMA Size	00
Rated Current	9 A
Number of Poles	3P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type of Overload	Melting alloy 3
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
SCCR	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	10.00 in (254.00 mm)
Width	6.00 in (152.40 mm)
Depth	5.56 in (141.22 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	UL Listed CSA NEMA

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	21191 - 8502,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901041955
Nbr. of units in pkg.	1
Package weight(Lbs)	7.34 lb(US) (3.33 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	6.30 in (16.002 cm)
Package 1 width	6.40 in (16.256 cm)
Package 1 Length	10.60 in (26.924 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------