



### Main

|                                 |                                  |
|---------------------------------|----------------------------------|
| Range of product                | Harmony 9001K                    |
| Product or component type       | Complete illuminated push-button |
| Device short name               | 9001K                            |
| Bezel material                  | Chromium plated metal            |
| Mounting diameter               | 1.18 in (30 mm)                  |
| Operator additional information | Extended metallic guard          |
| Light source                    | Red LED                          |

### Complementary

|                              |                        |
|------------------------------|------------------------|
| Shape of signaling unit head | Round                  |
| Type of operator             | Spring return          |
| Operator profile             | Red flush, unmarked    |
| Bulb base                    | BA 9s                  |
| Light block supply           | Direct 120 V AC/DC     |
| Mechanical durability        | 5000000 cycles         |
| Operating position           | Any position           |
| Net Weight                   | 0.37 lb(US) (0.166 kg) |

### Environment

|                                       |  |
|---------------------------------------|--|
| Standards                             | EN/IEC 60947-5-4<br>JIS C 4520<br>UL 508<br>CSA C22.2 No 14<br>EN/IEC 60947-5-1<br>JIS C 852<br>EN/IEC 60947-1 |
| Product certifications                | UL 508<br>NEMA   |
| Protective treatment                  | TC   |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)   |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C)   |
| Vibration resistance                  | 7 gn 2...500 Hz)IEC 60068-2-6  |
| Shock resistance                      | 50 gn IEC 60068-2-27   |
| Electrical shock protection class     | Class II IEC 61140   |
| IP degree of protection               | IP66 IEC 60529   |
| NEMA degree of protection             | NEMA 1<br>NEMA 12<br>NEMA 13<br>NEMA 2<br>NEMA 3<br>NEMA 3R<br>NEMA 4  |

## Ordering and shipping details

|                       |                               |
|-----------------------|-------------------------------|
| Category              | 21426 - 9001 K (NOT KA,KM,KX) |
| Discount Schedule     | CS1                           |
| GTIN                  | 00785901608745                |
| Nbr. of units in pkg. | 1                             |
| Package weight(Lbs)   | 0.5 lb(US) (0.23 kg)          |
| Returnability         | No                            |
| Country of origin     | MX                            |

## Packing Units

|                  |                      |
|------------------|----------------------|
| Package 1 Height | 5.08 in (12.903 cm)  |
| Package 1 width  | 2.00 in (5.080 cm)   |
| Package 1 Length | 12.90 in (32.774 cm) |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>  |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|