

Product data sheet

Characteristics

CUM400CB

Meter mains, QO, combination service entrance, ringed socket, 400A, surface mount, class 320, test block bypass



Main

Product or component type	Meter Mains
Range of product	QO

Complementary

Line Rated Current	400 A
Short-circuit current	25 kA
Network number of phases	1
Meter socket type	Ringed
Mounting	Surface Semi flush field installed flange kit
Number of spaces	0
Number of circuits	0
Number of Tandem Breakers	0
Hub type	A-L
Electrical connection	Lugs service ground Studs line side
Wire Size	AWG 4...250 kcmil aluminium)service ground AWG 4...250 kcmil copper)service ground
Disconnect	Service disconnect (factory installed)
Main Breaker Rating	400 A
Branch Breaker Rating	200 A
Service feed location	UG
Bypass type	Test block bypass Class 320
Height	43.00 in (1092.20 mm)
Width	28.25 in (717.55 mm)
Depth	7.87 in (199.90 mm)

Environment

Product certifications	UL E-6294
------------------------	-----------

Ordering and shipping details

Category	00148 - HOMELINE CSED DEVICES
Discount Schedule	DE3A
GTIN	00785901539544
Nbr. of units in pkg.	1
Package weight(Lbs)	115 lb(US) (52.16 kg)

Returnability	No
Country of origin	MX

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------