



## Main

Range of product	125 A Frame EDB-EGB-EJB
Product or component type	Miniature circuit-breaker
Device short name	EGB
Module type	E-Frame
Trip unit rating	875 A

## Complementary

Line Rated Current	30 A
Maximum operating voltage	277 V AC
AWG gauge	AWG 12...AWG 6 aluminium AWG 14...AWG 6 copper
Breaking capacity	35 KA 277 V AC 35 KA 240 V AC 65 KA 120 V AC 35 kA 120/240 V AC
Circuit breaker application	HID rated HACR rated
Electrical connection	Lugs aluminium
Holding current	270 A
Local signalling	Trip indicator
Mounting mode	Bolt-on
Number of poles	1
Number of spaces	1
Number of spaces required	1
Product destination	NF panelboard
Protection type	Short-circuit Overload
Trip unit technology	Thermal-magnetic
Breaking capacity code	G
Tightening torque	30.09 lbf.in (3.4 N.m) 0.00...0.02 in <sup>2</sup> (2.5...16 mm <sup>2</sup> ) (AWG 14...AWG 6)
Height	5.66 in (143.76 mm)
Width	0.98 in (24.89 mm)
Depth	4.05 in (102.87 mm)
Net Weight	2 lb(US) (0.91 kg)

## Environment

Product certifications	CULus
Ambient air temperature for operation	104 °F (40 °C)

## Ordering and shipping details

Category	00936 - EGB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901311096
Nbr. of units in pkg.	1
Package weight(Lbs)	1.35 lb(US) (0.61 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	2.20 in (5.588 cm)
Package 1 width	6.30 in (16.002 cm)
Package 1 Length	10.70 in (27.178 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------