

## SmartPro 208 & 120V 5kVA 3.75kW Line-Interactive Sine Wave UPS, 3U, Extended Run, Network Card Options, USB, DB9

MODEL NUMBER: **SMART5000XFMRXL**



### Description

Tripp Lite 5kVA Smart RM UPS. 5000VA line-interactive UPS for server, network and telecommunications equipment. UPS with internal batteries requires 3 rack spaces installed. Accepts 208V nominal input voltage. Simultaneous 208 & 120V output. Corrects brownouts and overvoltages from 167V to 260V. Sine wave output. Maintains battery-derived AC output during blackouts and severe voltage fluctuations. Expandable runtime with optional external battery packs. 11 output receptacles. NEMA L6-30P input connection with support for user-supplied 50A or hardwire input. Network-grade AC surge and noise suppression. Network management interfaces include USB, DB9 serial and slot for Network Management Card options. Supports simultaneous detailed monitoring of equipment load levels, self-test data and utility power conditions via all network interfaces simultaneously. PowerAlert UPS monitoring software is available via free download. Emergency Power Off (EPO) interface. Integrated 8-bank switched PDU. 3-stage metered current monitoring and battery charge LEDs. Utility power and voltage regulation LEDs. Audible alarm. Self-test. 4-post rack mounting accessories included; 2-9USTAND and 2POSTRMKITHD accessories available. Field-replaceable, hot-swappable internal batteries and battery packs.

### Features

- 5000VA/3750 watt max. output power capacity compatible with North American 208V/60Hz input voltage
- Supports full output at either 208V or 120V
- 3U rack/tower UPS installs in standard 19 inch rack enclosures with an installed depth of only 25 inches / 63.5cm
- Protects sensitive networking equipment from blackouts, voltage fluctuations and transient surges
- Line Interactive Automatic Voltage Regulation (AVR) corrects 208V nominal input from 167 to 260VAC back to usable 208/120V levels without consuming battery power
- AVR circuits boost undervoltages by 12% and reduce overvoltages by 12%
- Network interfaces support simultaneous communications via USB, DB9 serial and slot for Network

### Highlights

- 5kVA / 5000VA line interactive 3U rack/tower UPS; Sine wave output
- 208 & 120V output during brownouts to 167 and overvoltages to 260V
- USB, Serial, EPO & Network Management Card options
- 3U all-in-one chassis; 8 single-outlet switched load banks; 97% efficiency
- NEMA L6-30P input; 8 NEMA 5-15/20R, 2 L6-20R & 1 L6-30R outlets
- To use the Auto Probe feature, this product requires a WEBCARDLX network interface (sold separately) running LX firmware update 15.5.2 or later

### Package Includes

- SMART 5000XFMRXL UPS System
- USB & DB9 Serial Cabling
- Mounting hardware for 4-post rackmount installation
- Instruction manual



Management Card option

- Compatible with Tripp Lite UPS management card options TLNETCARD, WEBCARDLX and SNMPWEBCARD
- USB & Serial ports enable data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from [www.tripplite.com/poweralert](http://www.tripplite.com/poweralert)
- Built-in Emergency Power Off (EPO) interface with cable
- Sine wave output in AC and battery mode
- Expandable runtime with optional BP48V60RT-3U and BP48V27-2US external battery packs
- Half/full load runtime of 20/8.5 minutes with internal batteries
- Intelligent battery management system extends battery life
- Includes 11 output receptacles (2 L6-20, 1 L6-30 & 8 NEMA 5-15/20R)
- Ships with installed L6-30P input plug, supports user supplied 50A replacement plug or hardwire input
- Integrated 8 bank switched PDU enables remote outlet management for load shedding or remote reboot of individual devices
- 3 stage metered LEDs offer current monitoring and battery charge level
- Mains power and voltage regulation LEDs offer at-a-glance power status information
- Front panel switches support self-test and alarm cancel functions
- Included adjustable mounting rails support installation in 4 post 19 inch racks
- UPS ships fully assembled in full compliance with DOT regulations, no time consuming connection of internal batteries by user is required
- Supports upright tower placement with optional 2-9USTAND accessory

## Specifications

OVERVIEW	
UPC Code	037332121462
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	24A
Nominal Input Voltage(s) Supported	208V AC
UPS Input Connection Type	L6-30P
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	30A 208V
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	5000
Output kVA Capacity (kVA)	5
Output Watt Capacity (Watts)	3750





<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure, overload and low-battery conditions
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	1020
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Primary Form Factor	Rackmount
Cooling Method	Fan
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="http://www.tripplite.com/2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD">2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD</a> ); Tower ( <a href="http://www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND</a> )
Minimum Required Rack Depth with External Battery Pack (cm)	81
Minimum Required Rack Depth with External Battery Pack (in.)	32
Minimum Required Rack Depth without External Battery Pack (cm)	76
Minimum Required Rack Depth without External Battery Pack (in.)	30
Primary UPS Depth (mm)	635
Primary UPS Height (mm)	132
Primary UPS Width (mm)	445
Rack Height	3U
Shipping Dimensions (hwd / cm)	30.48 x 58.42 x 83.82
Shipping Dimensions (hwd / in.)	12.00 x 23.00 x 33.00
Shipping Weight (kg)	86.79
Shipping Weight (lbs.)	191.33
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	13.21 x 44.45 x 63.50



UPS Power Module Dimensions (hwd, in.)	5.2 x 17.5 x 25
UPS Power Module Weight (kg)	65.00
UPS Power Module Weight (lbs.)	143.3
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	5 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	366
AC Mode Efficiency Rating (100% Load)	97%
Audible Noise	45 dBA maximum, front side 1m
<b>COMMUNICATIONS</b>	
Network Management Cards	<a href="http://www.tripplite.com/SNMP-Web-Management-Accessory-Card-SmartPro-SmartOnline-UPS-Systems~SNMPWEBCARD">SNMPWEBCARD</a> <a href="http://www.tripplite.com/Web-Management-Accessory-Card-SmartPro-SmartOnline-UPS-Systems~TLNETCARD">TLNETCARD</a> <a href="http://www.tripplite.com/Web-Management-Accessory-Card~WEBCARDLX">WEBCARDLX</a>
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at <a href="https://www.tripplite.com/poweralert">https://www.tripplite.com/poweralert</a>
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network Management Card Description	Network management card optional
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	7 ms (AC to Battery); 1 ms (Battery to AC) typical
Low Voltage Transfer to Battery Power (Setpoint)	167
High Voltage Transfer to Battery Power (Setpoint)	260
<b>FEATURES &amp; SPECIFICATIONS</b>	
Grounding Lug	Back panel grounding lug
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring and Reboot (requires WEBCARDLX); Automatic Voltage Regulation (AVR); Expandable battery backup; Hot swappable batteries; Remote management; Sine wave output; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks



<b>STANDARDS &amp; COMPLIANCE</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI)
Certification Details	UL 1778:2005 R10.11, IEC 62040-1:2008; CAN/CSA-C22.2 NO 107.3-05+A1:06
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: <a href="http://www.tripplite.com/support/product-warranty-registration">Registration is required</a> for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 <a href="http://www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>