

PURELL® Hand Sanitizing Wipes

Version 1.1

SDS Number: 400000000481

Revision Date: 02/14/2020

SECTION 1. IDENTIFICATION

Product name : PURELL® Hand Sanitizing Wipes

Manufacturer or supplier's details

Company name of supplier : GOJO Industries, Inc.

Address : One GOJO Plaza, Suite 500
Akron, Ohio 44311

Telephone : 1 (330) 255-6000

Emergency telephone : CHEMTREC 1-800-424-9300
number CHEMTREC +1-703-527-3887: Outside USA & CANADA**Recommended use of the chemical and restrictions on use**

Recommended use : Hand Sanitizer

Restrictions on use : This is a personal care or cosmetic product that is safe for consumers and other users under normal and reasonably foreseeable use. Cosmetics and consumer products, specifically defined by regulations around the world, are exempt from the requirement of an SDS for the consumer. While this material is not considered hazardous, this SDS contains valuable information critical to the safe handling and proper use of the product for industrial workplace conditions as well as unusual and unintended exposures such as large spills. This SDS should be retained and available for employees and other users of this product. For specific intended-use guidance, please refer to the information provided on the package or instruction sheet.

SECTION 2. HAZARDS IDENTIFICATION**GHS Classification**

Eye irritation : Category 2A

GHS label elements

Hazard pictograms :



Signal word : Warning

Hazard statements : H319 Causes serious eye irritation.

Precautionary statements : **Prevention:**
P280 Wear eye protection/ face protection.
Response:
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337 + P313 If eye irritation persists: Get medical advice/

PURELL® Hand Sanitizing Wipes

Version 1.1

SDS Number: 400000000481

Revision Date: 02/14/2020

attention.

Other hazards

None known.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**Hazardous components**

Chemical name	CAS-No.	Concentration (%)
Benzalkonium Chloride	68391-01-5	≥ 0.1 - < 0.25

SECTION 4. FIRST AID MEASURES

General advice	: In the case of accident or if you feel unwell, seek medical advice immediately. When symptoms persist or in all cases of doubt seek medical advice.
If inhaled	: If inhaled, remove to fresh air. If symptoms persist, call a physician.
In case of skin contact	: Wash with water and soap as a precaution. Get medical attention if irritation develops and persists.
In case of eye contact	: In case of contact, immediately flush eyes with plenty of water for at least 15 minutes. If easy to do, remove contact lens, if worn. Seek medical advice.
If swallowed	: If swallowed, DO NOT induce vomiting. Rinse mouth with water. Obtain medical attention.
Most important symptoms and effects, both acute and delayed	: Causes serious eye irritation.
Protection of first-aiders	: First Aid responders should pay attention to self-protection and use the recommended protective clothing

SECTION 5. FIREFIGHTING MEASURES

Suitable extinguishing media	: Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.
Unsuitable extinguishing media	: None known.
Specific hazards during firefighting	: Exposure to decomposition products may be a hazard to health. No hazardous combustion products are known
Hazardous combustion products	: No hazardous combustion products are known
Specific extinguishing methods	: Use extinguishing measures that are appropriate to local circumstances and the surrounding environment. Use water spray to cool unopened containers.
Further information	: Collect contaminated fire extinguishing water separately. This must not be discharged into drains. Fire residues and contaminated fire extinguishing water must

**PURELL® Hand Sanitizing Wipes**

Version 1.1

SDS Number: 400000000481

Revision Date: 02/14/2020

Special protective equipment for firefighters	: be disposed of in accordance with local regulations. : In the event of fire, wear self-contained breathing apparatus. : Use personal protective equipment.
---	--

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures	: Use personal protective equipment. : Ensure adequate ventilation. : Material can create slippery conditions.
Environmental precautions	: Discharge into the environment must be avoided. : Prevent further leakage or spillage if safe to do so. : Prevent spreading over a wide area (e.g. by containment or oil barriers). : Retain and dispose of contaminated wash water. : Local authorities should be advised if significant spillages cannot be contained.
Methods and materials for containment and cleaning up	: Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13). : Keep in suitable, closed containers for disposal. : Clean contaminated floors and objects thoroughly while observing environmental regulations.

SECTION 7. HANDLING AND STORAGE

Advice on safe handling	: For personal protection see section 8. : Do not swallow. : Avoid contact with eyes. : Keep container closed when not in use.
Conditions for safe storage	: Keep in properly labelled containers. : Keep container tightly closed in a dry and well-ventilated place. : Store in accordance with the particular national regulations.

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Components with workplace control parameters**

Contains no substances with occupational exposure limit values.

Personal protective equipment

Respiratory protection	: No personal respiratory protective equipment normally required.
Eye protection	: No special measures necessary provided product is used correctly. : Wear face-shield and protective suit for abnormal processing problems.
Skin and body protection	: No special measures necessary provided product is used correctly.
Protective measures	: Choose body protection in relation to its type, to the concentration and amount of dangerous substances, and to

PURELL® Hand Sanitizing Wipes

Version 1.1

SDS Number: 400000000481

Revision Date: 02/14/2020

Hygiene measures : the specific work-place.
Ensure that eye flushing systems and safety showers are located close to the working place.
: Handle in accordance with good industrial hygiene and safety practice.
Avoid contact with eyes.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : sheets
Colour : clear, cloudy, colourless, light yellow
Odour : citrus
Odour Threshold : No data available

pH : 5.5 - 8.5, (20 °C)

Melting point/freezing point : No data available
Boiling point/boiling range : 99.00 °C

Flash point : > 100.00 °C

Evaporation rate : No data available

Flammability (solid, gas) : Not applicable

Flammability (liquids) :

Upper explosion limit : No data available

Lower explosion limit : No data available

Vapour pressure : No data available

Relative vapour density : No data available

Density : 0.9986 g/cm3

Solubility(ies)
Water solubility : soluble

Partition coefficient: n-octanol/water : Not applicable

Auto-ignition temperature : No data available

Thermal decomposition : The substance or mixture is not classified self-reactive.

Viscosity
Viscosity, kinematic : 75 mm2/s (25 °C)

Explosive properties : Not explosive

Oxidizing properties : The substance or mixture is not classified as oxidizing.

SECTION 10. STABILITY AND REACTIVITY

**PURELL® Hand Sanitizing Wipes**

Version 1.1

SDS Number: 400000000481

Revision Date: 02/14/2020

Reactivity	: Not classified as a reactivity hazard.
Chemical stability	: Stable under normal conditions.
Incompatible materials	: Oxidizing agents
Hazardous decomposition products	: No hazardous decomposition products are known.

SECTION 11. TOXICOLOGICAL INFORMATION**Information on likely routes of exposure**

Inhalation
Eye contact
Skin contact

Acute toxicity

Not classified based on available information.

Components:**Benzalkonium Chloride:**

Acute oral toxicity : LD50 (Rat): 850 mg/kg

Acute dermal toxicity : LD50 (Rat): 2,300 mg/kg

Skin corrosion/irritation

Not classified based on available information.

Components:**Benzalkonium Chloride:**

Species: Rabbit

Result: Corrosive after 3 minutes to 1 hour of exposure

Remarks: Based on data from similar materials

Serious eye damage/eye irritation

Causes serious eye irritation.

Product:

Result: Irritating to eyes.

Components:**Benzalkonium Chloride:**

Species: Rabbit

Result: Irreversible effects on the eye

Remarks: Based on data from similar materials

Respiratory or skin sensitisation

Skin sensitisation: Not classified based on available information.

Respiratory sensitisation: Not classified based on available information.

Components:**Benzalkonium Chloride:**

Test Type: Buehler Test

Exposure routes: Skin contact

Species: Guinea pig

**PURELL® Hand Sanitizing Wipes**

Version 1.1

SDS Number: 400000000481

Revision Date: 02/14/2020

Method: OECD Test Guideline 406
Result: negative
Remarks: Based on data from similar materials

Germ cell mutagenicity

Not classified based on available information.

Components:**Benzalkonium Chloride:**

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Method: OECD Test Guideline 471
Result: negative
Remarks: Based on data from similar materials

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo
cytogenetic assay)
Test species: Mouse
Application Route: Ingestion
Method: OECD Test Guideline 474
Result: negative
Remarks: Based on data from similar materials

Carcinogenicity

Not classified based on available information.

IARC No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

OSHA No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

NTP No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Reproductive toxicity

Not classified based on available information.

Components:**Benzalkonium Chloride:**

Effects on fertility : Test Type: Two-generation reproduction toxicity study
Species: Rat
Application Route: Ingestion
Result: negative
Remarks: Based on data from similar materials

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: Ingestion
Result: negative
Remarks: Based on data from similar materials

**PURELL® Hand Sanitizing Wipes**

Version 1.1

SDS Number: 400000000481

Revision Date: 02/14/2020

STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

Repeated dose toxicity**Components:****Benzalkonium Chloride:**

Species: Mouse

NOAEL: 192 mg/kg

Application Route: Ingestion

Exposure time: 94 d

Remarks: Based on data from similar materials

Aspiration toxicity

Not classified based on available information.

SECTION 12. ECOLOGICAL INFORMATION**Ecotoxicity****Components:****Benzalkonium Chloride:**

Toxicity to fish	: LC50 (Lepomis macrochirus (Bluegill sunfish)): 0.515 mg/l Exposure time: 96 h Remarks: Based on data from similar materials
Toxicity to daphnia and other aquatic invertebrates	: EC50 (Daphnia magna (Water flea)): 0.016 mg/l Exposure time: 48 h Method: Directive 67/548/EEC, Annex V, C.2. Remarks: Based on data from similar materials
Toxicity to algae	: ErC50 (Selenastrum capricornutum (green algae)): 0.049 mg/l Exposure time: 72 h Method: OECD Test Guideline 201 Remarks: Based on data from similar materials EC10 (Selenastrum capricornutum (green algae)): 0.009 mg/l Exposure time: 72 h Method: OECD Test Guideline 201 Remarks: Based on data from similar materials
M-Factor (Acute aquatic toxicity)	: 10
Toxicity to fish (Chronic toxicity)	: NOEC (Pimephales promelas (fathead minnow)): 0.0322 mg/l Exposure time: 34 d Remarks: Based on data from similar materials
Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity)	: NOEC (Daphnia magna (Water flea)): 0.0125 mg/l Exposure time: 21 d Method: OECD Test Guideline 211 Remarks: Based on data from similar materials

**PURELL® Hand Sanitizing Wipes**

Version 1.1

SDS Number: 400000000481

Revision Date: 02/14/2020

M-Factor (Chronic aquatic toxicity) : 1

Persistence and degradability**Components:****Benzalkonium Chloride:**

Biodegradability : Result: Readily biodegradable.
Biodegradation: 72 %
Exposure time: 28 d

Bioaccumulative potential**Components:****Benzalkonium Chloride:**

Partition coefficient: n-octanol/water : log Pow: 2.75
Remarks: Based on data from similar materials

Mobility in soil

No data available

Other adverse effects

No data available

Product:

Regulation 40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances

Remarks This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

SECTION 13. DISPOSAL CONSIDERATIONS**Disposal methods**

Waste from residues : Dispose of in accordance with local regulations.
Contaminated packaging : Dispose of as unused product.
Empty containers should be taken to an approved waste handling site for recycling or disposal.

SECTION 14. TRANSPORT INFORMATION**International Regulation****IATA-DGR**

Not regulated as a dangerous good

IMDG-Code

Not regulated as a dangerous good

National Regulations**49 CFR**

Not regulated as a dangerous good

**PURELL® Hand Sanitizing Wipes**

Version 1.1

SDS Number: 400000000481

Revision Date: 02/14/2020

SECTION 15. REGULATORY INFORMATION**EPCRA - Emergency Planning and Community Right-to-Know Act****CERCLA Reportable Quantity**

This material does not contain any components with a CERCLA RQ.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Acute Health Hazard

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

Clean Air Act

This product does not contain any hazardous air pollutants (HAP), as defined by the U.S. Clean Air Act Section 12 (40 CFR 61).

This product does not contain any chemicals listed under the U.S. Clean Air Act Section 112(r) for Accidental Release Prevention (40 CFR 68.130, Subpart F).

This product does not contain any chemicals listed under the U.S. Clean Air Act Section 111 SOCM Intermediate or Final VOC's (40 CFR 60.489).

This product does not contain any VOC exemptions listed under the U.S. Clean Air Act Section 450.

Clean Water Act

This product does not contain any toxic pollutants listed under the U.S. Clean Water Act Section 307

US State Regulations**Massachusetts Right To Know**

No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know

Water (Aqua)	7732-18-5	90 - 100 %
Phenoxyethanol	122-99-6	0.1 - 1 %

New Jersey Right To Know

Water (Aqua)	7732-18-5	90 - 100 %
--------------	-----------	------------

California Prop 65

This product does not require a warning label under California Proposition 65.

The components of this product are reported in the following inventories:

TSCA : On TSCA Inventory

AICS : On the inventory, or in compliance with the inventory

DSL : All components of this product are on the Canadian DSL.

PURELL® Hand Sanitizing Wipes

Version 1.1


SDS Number: 400000000481

Revision Date: 02/14/2020

ENCS	: On the inventory, or in compliance with the inventory
ISHL	: On the inventory, or in compliance with the inventory
KECI	: On the inventory, or in compliance with the inventory
PICCS	: On the inventory, or in compliance with the inventory
IECSC	: On the inventory, or in compliance with the inventory
NZIoC	: On the inventory, or in compliance with the inventory

Inventories

AICS (Australia), DSL (Canada), IECSC (China), REACH (European Union), ENCS (Japan), ISHL (Japan), KECI (Korea), NZIoC (New Zealand), PICCS (Philippines), TCSI (Taiwan), TSCA (USA)

SECTION 16. OTHER INFORMATION**Further information****NFPA:****HMIS III:**

HEALTH	2
FLAMMABILITY	1
PHYSICAL HAZARD	0

0 = not significant, 1 = Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

Revision Date : 02/14/2020

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.