



## Main

Range of product	125 A Frame EDB-EGB-EJB
Product or component type	Miniature circuit-breaker
Device short name	EGB
Module type	E-Frame
Trip unit rating	1800 A

## Complementary

Line Rated Current	40 A
Maximum operating voltage	277 V AC
AWG gauge	AWG 12...AWG 2/0 aluminium AWG 14...AWG 2/0 copper
Breaking capacity	35 KA 277 V AC 35 KA 240 V AC 65 KA 120 V AC 35 kA 120/240 V AC
Circuit breaker application	HID rated HACR rated
Electrical connection	Lugs aluminium
Holding current	630 A
Local signalling	Trip indicator
Mounting mode	Bolt-on
Number of poles	1
Number of spaces	1
Number of spaces required	1
Product destination	NF panelboard
Protection type	Overload Short-circuit
Trip unit technology	Thermal-magnetic
Breaking capacity code	G
Tightening torque	34.52 lbf.in (3.9 N.m) 0.00...0.01 in <sup>2</sup> (2.5...6 mm <sup>2</sup> ) (AWG 14...AWG 10) 49.56 lbf.in (5.6 N.m) 0.02...0.11 in <sup>2</sup> (10...70 mm <sup>2</sup> ) (AWG 8...AWG 2/0)
Height	5.66 in (143.76 mm)
Width	0.98 in (24.89 mm)
Depth	4.05 in (102.87 mm)
Net Weight	2 lb(US) (0.91 kg)

## Environment

Product certifications	CULus
Ambient air temperature for operation	104 °F (40 °C)

## Ordering and shipping details

Category	00936 - EGB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901311102
Nbr. of units in pkg.	1
Package weight(Lbs)	1.28 lb(US) (0.58 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	1.80 in (4.572 cm)
Package 1 width	6.00 in (15.240 cm)
Package 1 Length	10.10 in (25.654 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------