



SAFETY DATA SHEET

1. Product and Company Identification

Product identifier	Pan-Treat (4296-60)
Other means of identification	Not available
Recommended use	Condensate drain pan treatment
Recommended restrictions	None known.
Manufacturer information	Nu-Calgon 2611 Schuetz Road St. Louis, MO 63043 US Phone: 314-469-7000 / 800-554-5499 Emergency Phone: 1-800-424-9300 (CHEMTREC)
Supplier	See above.

2. Hazards Identification

Physical hazards	Not classified.	
Health hazards	Acute toxicity, oral	Category 4
	Skin corrosion/irritation	Category 2
	Serious eye damage/eye irritation	Category 1
Environmental hazards	Not classified.	
WHMIS 2015 defined hazards	Not classified	
Label elements		



Signal word	Danger
Hazard statement	Harmful if swallowed. Causes skin irritation. Causes serious eye damage.
Precautionary statement	
Prevention	Wash thoroughly after handling. Do not eat, drink or smoke when using this product. Wear protective gloves/protective clothing/eye protection/face protection.
Response	IF ON SKIN: Wash with plenty of water. Specific treatment (see information on this label). If skin irritation occurs: Get medical advice/attention. Take off contaminated clothing and wash it before reuse. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. IF SWALLOWED: Call a POISON CENTER or doctor/physician if you feel unwell. Rinse mouth.
Storage	Store away from incompatible materials.
Disposal	Dispose of contents/container in accordance with local/regional/national/international regulations.
WHMIS 2015: Health Hazard(s) not otherwise classified (HHNOC)	None known
WHMIS 2015: Physical Hazard(s) not otherwise classified (PHNOC)	None known
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	None.

3. Composition/Information on Ingredients

Mixture			
Chemical name	Common name and synonyms	CAS number	%
Benzyl-C12-18-alkyldimethyl ammonium chlorides		68391-01-5	10-30*
Urea		57-13-6	45-70*

All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

Composition comments

US GHS: The exact percentage (concentration) of composition has been withheld as a trade secret in accordance with paragraph (i) of §1910.1200.

*CANADA GHS: The exact percentage (concentration) of composition has been withheld as a trade secret.

4. First Aid Measures

Inhalation	If symptoms develop, move victim to fresh air. If symptoms persist, obtain medical attention. If breathing has stopped, trained personnel should administer CPR immediately.
Skin contact	IF ON SKIN: Wash with plenty of water. If skin irritation occurs: Get medical advice/attention. Take off contaminated clothing and wash it before reuse. Specific treatment (see information on this label).
Eye contact	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER/doctor.
Ingestion	IF SWALLOWED: Call a POISON CENTER/doctor if you feel unwell. Rinse mouth.
Most important symptoms/effects, acute and delayed	Causes serious eye damage. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Permanent eye damage including blindness could result.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved and take precautions to protect themselves. In the case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).

5. Fire Fighting Measures

Suitable extinguishing media	Water spray. Fog. Foam. Dry chemical powder. Carbon dioxide.
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire-fighting equipment/instructions	In the event of fire, cool tanks with water spray.
Specific methods	Cool containers exposed to flames with water until well after the fire is out.
General fire hazards	No unusual fire or explosion hazards noted.
Hazardous combustion products	May include and are not limited to: Oxides of carbon. Hydrogen chloride. Oxides of nitrogen.

6. Accidental Release Measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep out of low areas. Keep people away from and upwind of spill/leak. Wear appropriate protective equipment and clothing during clean-up. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Stop the flow of material, if this is without risk. Following product recovery, flush area with water. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid discharge into drains, water courses or onto the ground.

7. Handling and Storage

Precautions for safe handling	Do not taste or swallow. Avoid prolonged exposure. Provide adequate ventilation. Wear appropriate personal protective equipment. Observe good industrial hygiene practices. When using, do not eat, drink or smoke. Wash hands thoroughly after handling. Avoid contact with eyes, skin and clothing.
Conditions for safe storage, including any incompatibilities	Keep container tightly closed. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure Controls/Personal Protection

Occupational exposure limits

US. AIHA Workplace Environmental Exposure Level (WEEL) Guides

Components	Type	Value	Form
Urea (CAS 57-13-6)	TWA	10 mg/m3	Total particulate.

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

Eye/face protection

Wear safety glasses with side shields (or goggles) and a face shield.

Skin protection

Hand protection

Impervious gloves. Confirm with reputable supplier first.

Other

As required by employer code. Wear appropriate chemical resistant clothing.

Respiratory protection

Where exposure guideline levels may be exceeded, use an approved NIOSH respirator. Respirator should be selected by and used under the direction of a trained health and safety professional following requirements found in OSHA's respirator standard (29 CFR 1910.134), CAN/CSA-Z94.4 and ANSI's standard for respiratory protection (Z88.2).

Thermal hazards

Not available.

General hygiene considerations

When using, do not eat, drink or smoke. Wash hands after handling and before eating.

9. Physical and Chemical Properties

Appearance	Crystalline.
Physical state	Solid.
Form	Solid. Tablets
Color	Green
Odor	Coconut
Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not available.
Pour point	Not available.
Specific gravity	0.981
Partition coefficient (n-octanol/water)	Not available.
Flash point	Not available.
Evaporation rate	Not available.
Flammability (solid, gas)	Not applicable.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	Not available.
Vapor density	Not available.
Relative density	Not available.
Solubility(ies)	100 %
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.

10. Stability and Reactivity

Reactivity	Do not mix with other chemicals.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Chemical stability	Stable under recommended storage conditions.
Conditions to avoid	Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	May include and are not limited to: Oxides of carbon. Oxides of nitrogen. Hydrogen chloride.

11. Toxicological Information

Routes of exposure		Inhalation. Ingestion. Skin contact. Eye contact.	
Information on likely routes of exposure			
Ingestion	Harmful if swallowed.		
Inhalation	Prolonged inhalation may be harmful. May cause irritation to the respiratory system.		
Skin contact	Not corrosive to skin based on in-vitro test data (OECD Guideline 435 - Corrositex®).		
Eye contact	Causes serious eye damage.		
Symptoms related to the physical, chemical and toxicological characteristics		Causes serious eye damage. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Permanent eye damage including blindness could result.	
Information on toxicological effects			
Acute toxicity		Harmful if swallowed.	
Components		Species	Test Results
Benzyl-C12-18-alkyldimethyl ammonium chlorides (CAS 68391-01-5)			
Acute			
Dermal			
LD50	Rat	1420 mg/kg, HSDB	
Inhalation			
LC50	Not available		
Oral			
LD50	Mouse	150 mg/kg, HSDB	
	Rat	300 mg/kg, HSDB	
		240 mg/kg, HSDB	
Urea (CAS 57-13-6)			
Acute			
Dermal			
LD50	Not available		
Inhalation			
LC50	Not available		
Oral			
LD50	Mouse	13000 mg/kg, ECHA	
		11500 mg/kg, ECHA	
		11000 mg/kg, CCOHS	
	Rat	15000 mg/kg, ECHA	
		14300 mg/kg	
	Sheep	28500 mg/kg	
Skin corrosion/irritation		Not corrosive to skin based on in-vitro test data (OECD Guideline 435 - Corrositex®).	
Exposure minutes	Not available.		
Erythema value	Not available.		
Oedema value	Not available.		
Serious eye damage/eye irritation		Causes serious eye damage.	
Corneal opacity value	Not available.		

Iris lesion value	Not available.
Conjunctival reddening value	Not available.
Conjunctival oedema value	Not available.
Recover days	Not available.
Respiratory or skin sensitization	
Respiratory sensitization	Not available.
Skin sensitization	Not applicable.
Mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP or OSHA.
US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)	
	Not listed.
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
Teratogenicity	Not available.
Specific target organ toxicity - single exposure	Not classified.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	Not available.
Chronic effects	Prolonged inhalation may be harmful.

12. Ecological Information

Ecotoxicity	See below		
Ecotoxicological data			
Components		Species	Test Results
Urea (CAS 57-13-6)			
Crustacea	EC50	Daphnia	10000 mg/L, 48 Hours
Aquatic			
Crustacea	EC50	Water flea (Daphnia magna)	3910 mg/L, 48 hours
Fish	LC50	Giant gourami (Colisa fasciata)	5 mg/L, 96 hours
Persistence and degradability	No data is available on the degradability of this product.		
Bioaccumulative potential	No data available.		
Mobility in soil	No data available.		
Mobility in general	Not available.		
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.		

13. Disposal Considerations

Disposal instructions	Collect and reclaim or dispose in sealed containers at licensed waste disposal site. This material and its container must be disposed of as hazardous waste. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of contents/container in accordance with local/regional/national/international regulations.
Local disposal regulations	Dispose in accordance with all applicable regulations.
Hazardous waste code	The waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Waste from residues / unused products	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Empty containers should be taken to an approved waste handling site for recycling or disposal. Since emptied containers may retain product residue, follow label warnings even after container is emptied.

14. Transport Information

Transport of Dangerous Goods (TDG) Proof of Classification	Classification Method: Classified as per Part 2, Sections 2.1 – 2.8 of the Transportation of Dangerous Goods Regulations. If applicable, the technical name and the classification of the product will appear below.
---	--

U.S. Department of Transportation (DOT)

Not regulated as dangerous goods.

Transportation of Dangerous Goods (TDG - Canada)

Not regulated as dangerous goods.

IATA/ICAO (Air)

Not regulated as dangerous goods.

IMDG (Marine Transport)

Not regulated as dangerous goods.

15. Regulatory Information

Canadian federal regulations This product has been classified in accordance with the hazard criteria of the HPR and the SDS contains all the information required by the HPR.

Export Control List (CEPA 1999, Schedule 3)

Not listed.

Greenhouse Gases

Not listed.

Precursor Control Regulations

Not regulated.

WHMIS 2015 Exemptions

Not applicable

US federal regulations

This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

The chemicals listed in Section 3 are on the TSCA Chemical Substances Inventory.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)**Hazard categories**

Immediate Hazard - Yes
Delayed Hazard - No
Fire Hazard - No
Pressure Hazard - No
Reactivity Hazard - No

SARA 302 Extremely hazardous substance

No

SARA 311/312 Hazardous chemical

No

SARA 313 (TRI reporting)

Not regulated.

Other federal regulations**Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List**

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

US state regulations

See below

US - Minnesota Haz Subs: Listed substance

Urea (CAS 57-13-6) Listed.

US - Texas Effects Screening Levels: Listed substance

Benzyl-C12-18-alkyldimethyl ammonium chlorides (CAS 68391-01-5) Listed.

Urea (CAS 57-13-6) Listed.

US. Massachusetts RTK - Substance List

Not regulated.

US. New Jersey Worker and Community Right-to-Know Act

Not regulated.

US. Pennsylvania Worker and Community Right-to-Know Law

Not listed.

US. Rhode Island RTK

Not regulated.

US. California Proposition 65

Not Listed.

Inventory status


Country(s) or region	Inventory name	On inventory (yes/no)*
Canada	Domestic Substances List (DSL)	No
Canada	Non-Domestic Substances List (NDSL)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

16. Other Information

LEGEND	
Severe	4
Serious	3
Moderate	2
Slight	1
Minimal	0

HEALTH	/ 3
FLAMMABILITY	0
PHYSICAL HAZARD	0
PERSONAL PROTECTION	X



Disclaimer

Information contained herein was obtained from sources considered technically accurate and reliable. While every effort has been made to ensure full disclosure of product hazards, in some cases data is not available and is so stated. Since conditions of actual product use are beyond control of the supplier, it is assumed that users of this material have been fully trained according to the requirements of all applicable legislation and regulatory instruments. No warranty, expressed or implied, is made and supplier will not be liable for any losses, injuries or consequential damages which may result from the use of or reliance on any information contained in this document. The information in the sheet was written based on the best knowledge and experience currently available.

Issue date

21-August-2018

Version #

01

Effective date

21-August-2018

Prepared by

Nu-Calgon Technical Service Phone: (314) 469-7000