



Main

Range of product	Altivar
Product or component type	EMC input filter
Range compatibility	Altivar Process ATV900 Altivar Machine ATV340 Altivar Process ATV600
Product compatibility	Variable speed drive ATV630 wall mount, 75 kW, 380...480 V Variable speed drive ATV630 wall mount, 90 kW, 380...480 V Variable speed drive ATV630 wall mount, 45 kW, 200...240 V Variable speed drive ATV650 wall mount, 75 kW, 380...480 V Variable speed drive ATV650 wall mount, 90 kW, 380...480 V Variable speed drive ATV930 wall mount, 75 kW, 380...480 V Variable speed drive ATV930 wall mount, 90 kW, 380...480 V Variable speed drive ATV930 wall mount, 45 kW, 200...240 V Variable speed drive ATV950 wall mount, 75 kW, 380...480 V Variable speed drive ATV950 wall mount, 90 kW, 380...480 V Variable speed drive ATV34055 kW, 380...480 V Variable speed drive ATV34075 kW, 380...480 V
Product specific application	Radio interference input filter
Mounting location	At variable speed drive side
Line Rated Current	200 A
Thermal losses	32.5 W
Phase	Three phase

Complementary

Electrical connection	Terminal 150 mm ² 300 kcmil
Maximum motor cable length	492.13 Ft (150 m) shielded motor cable 4 kHz EN/IEC 61800-3 category C2, 380...480 V 300 M shielded motor cable 4 kHz conforming to EN/IEC 61800-3 category C3, 380...480 V 150 M shielded motor cable 4 kHz conforming to EN/IEC 61800-3 category C2, 200...240 V 300 M shielded motor cable 4 kHz conforming to EN/IEC 61800-3 category C3, 200...240 V 164.04 Ft (50 m) shielded motor cable 4 kHz EN/IEC 61800-3 category C1, 200...240 V 50 m shielded motor cable 4 kHz conforming to EN/IEC 61800-3 category C1, 380...480 V
Maximum earth leakage current	13.9 MA 400 V 50 Hz TN 13.9 mA 400 V 50 Hz TT
Power supply voltage	380...480 V 200...240 V
Tolerance	10 %
Mechanical robustness	Shocks class 3M4 IEC 60721-3-3 Vibrations class 3M4 IEC 60721-3-3
Width	7.87 in (200 mm)
Height	17.52 in (445 mm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Depth	12.60 in (320 mm)
Net Weight	20.94 lb(US) (9.5 kg)

Environment

IP degree of protection	IP20mounting side by side IP21with kit VW3A47908
Relative humidity	5...95 % without condensation IEC 61800-5-1
Ambient air temperature for operation	14...122 °F (-10...50 °C) without current derating) 122...140 °F (50...60 °C) with current derating 1.5 % per °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Operating altitude	0...1000 m without current derating 3280.84...13123.36 ft (1000...4000 m) with current derating 1 % per 100 m
Standards	EN/IEC 61800-3

Ordering and shipping details

Category	22184 - ATV340 ACCESSORIES
Discount Schedule	CP4B
GTIN	00785901764939
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	CN


Packing Units

Package 1 Height	2.800 dm
Package 1 width	5.300 dm
Package 1 Length	3.800 dm

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Dimensions




Dimensions in mm

A	B	C	A1	B1	Ø
200	445	320	140	415	11

Dimensions in in.

A	B	C	A1	B1	Ø
7.9	17.5	12.6	5.5	16.3	0.43

Recommended Schema



- (1) Filter
- (2) Drive