

Product data sheet

Characteristics

8903SQG1V02

Contacteur, Type S, multipole lighting, electrically held, 100A, 2 pole, 110/120VAC 50/60Hz coil, NEMA 1



Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	100 A
Number of Poles	2P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical connection	Lugs
Height	25.16 in (639 mm)
Depth	8.98 in (228 mm)
Width	11.26 in (286 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product certifications	UL Listed CSA

Ordering and shipping details

Category	21325 - 8903 S (NOT S°C) ELECT.
Discount Schedule	CP1
GTIN	00785901619444
Nbr. of units in pkg.	1
Package weight(Lbs)	34.37 lb(US) (15.59 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	10.60 in (26.924 cm)
Package 1 width	12.00 in (30.480 cm)
Package 1 Length	25.70 in (65.278 cm)

Offer Sustainability

EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------