

Product data sheet

Characteristics

8538SEA23V02S

NEMA Combination Starter, Type S, 100A fusible disconnect, Size 3, 90A, 50HP at 600VAC, 3 phase, 3 pole, melting alloy, 120VAC coil, NEMA 12



Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Number of Poles	3P
Horsepower Rating	50 Hp 460 V AC, 3 phase 50 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Thermal overload type	Melting alloy 3
Disconnect Type	Fusible disconnect switch H, 100 A
NEMA size	3

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
----------------	---

Ordering and shipping details

Category	21214 - 8538,39 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901458944
Nbr. of units in pkg.	1
Package weight(Lbs)	112 lb(US) (50.80 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	18.30 in (46.482 cm)
Package 1 width	13.70 in (34.798 cm)
Package 1 Length	37.20 in (94.488 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------