

SPEAKMAN® S-9129-CA-E

Sensorflo® Battery Powered Lavatory Faucet

FEATURES:

- Brass housing and brass spout.
- Solenoid with built-in filter.
- Two 3-volt DC lithium batteries.
- Above counter mechanical mixer.
- Manual override valve.
- Battery module with waterproof connectors.
- Includes 8 in. deck plate.
- Low battery warning light.
- 120-second time out feature.
- Lead-free construction.
- Water conserving vandal-resistant flow control reduces flow to 0.5 gpm (1.89 L/min).
- NOTE: stainless steel flexible supply hose(s), 3/8 in. compression, to supply stop(s) not included, see add-ons below.

COMPLIANCE:

- ASME A112.18.1/CSA B125.1 certified
- NSF 61 certified
- NSF 372 certified

FINISH:



PC

ADD-ONS:

- 0.5 gpm Boca spray outlet & 1.5 gpm laminar flow outlet kit A-BOLF
- Two (2) stainless steel flexible supply hoses to supply stops A-HS
- Under counter thermostatic mixing valve A-TMV
- 1.2 gpm laminar flow outlet A-ELF
- 1.2 gpm aerator A-EA12

WARRANTY:

- 5 Year Limited



DIMENSIONS: NOTE: 1. All dimensions are in inches (millimeters) unless otherwise specified and are subject to change without notice.
 2. Inlet is 3/8" compression with male threads. Position faucet as close to the edge of the sink as possible.

S-9129-CA-E

