

RA2

198# PAPER MEDIUM GRADE FILAMENT TAPE

DESCRIPTION

An all-purpose fiberglass reinforced paper backed strapping tape with pressure-sensitive natural rubber/resin adhesive. Medium tensile strength, high adhesion and medium impact. Operating temperature range: +32°F to +200°F (0°C to +93°C).

PRODUCT APPLICATIONS

General bundling, holding, palletizing and splicing applications.



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA
Customer Service: 800.IPG.8273 | 800.474.8273
Tape Technical Service: 877.447.4832
www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 11/13

INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

NOMINAL VALUES

The following data are nominal values based on PSTC, ASTM and other standard tests. The data should not be considered as specifications.

Backing	Medium Crepe Paper
Adhesive	Natural Rubber/Resin
Reinforcement	Fiberglass
Adhesion to Steel (oz/in of width) (at 90° peel angle) ASTM D-3330	40 (11 N/25mm)
Tensile Strength (lbs/in of width) ASTM D-3759	198 (867 N/25mm)
Elongation (% at break) ASTM D-3759	4
Quick Stick (oz/in of width) To Steel: To Kraft:	12 (3.3 N/25mm) 2 (0.5 N/25mm)
Total Thickness (mils) PSTC-133	9.8 (0.25 mm)
Color	Natural

