

HU362RBVW

Safety switch, heavy duty, non fusible, 60A, 3 poles, 60 hp, 600 VAC/DC, NEMA 3R, bolt-on hub, viewing window



Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device application	Heavy application
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	None
Phase	3 phase
Number of Poles	3
Current Rating	60 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 3R galvanized steel
Maximum Horse Power Rating	10 Hp 240 V at AC 50-60 Hz for 1 phase conforming to NEC 430.52 20 Hp 240 V at AC 50-60 Hz for 3 phase conforming to NEC 430.52 25 Hp 480 V at AC 50-60 Hz for 1 phase conforming to NEC 430.52 50 Hp 480 V at AC 50-60 Hz for 3 phase conforming to NEC 430.52 30 Hp 600 V at AC 50-60 Hz for 1 phase conforming to NEC 430.52 60 Hp 600 V at AC 50-60 Hz for 3 phase conforming to NEC 430.52 10 Hp 250 V at DC conforming to NEC 430.52 30 hp 600 V at DC

Complementary

Mounting Type	Surface
Wiring configuration	3-wire
Wire Size	AWG 14...AWG 3 copper AWG 12...AWG 3 aluminium
Tightening torque	50 Lbf.in (5.65 N.m) (AWG 3) 45 Lbf.in (5.08 N.m) (AWG 6...AWG 4) 40 Lbf.in (4.52 N.m) 0.01 in ² (8.367 mm ²) (AWG 8) 50 lbf.in (5.65 N.m) 0.00...0.01 in ² (2.06...5.261 mm ²) (AWG 14...AWG 10)
Depth	6.38 in (162.05 mm)
Width	10.5 in (266.70 mm)
Height	21.25 in (539.75 mm)
Net Weight	19.84 lb(US) (9 kg)

Environment

Certifications	UL listed file E2875
----------------	----------------------

Ordering and shipping details

Category	00117 - H&HU SW,VIEW WINDOW(VW)
Discount Schedule	DE1
GTIN	00785901527909
Nbr. of units in pkg.	1
Package weight(Lbs)	16 lb(US) (7.26 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	7.20 in (18.288 cm)
Package 1 width	10.80 in (27.432 cm)
Package 1 Length	19.90 in (50.546 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------