# **Barricade Ribbon** WEATHER RESISTANT SPECIALTY BARRICADE

TAPE

#### DESCRIPTION

An all-weather, UV, water and tear resistant barricade tape designed to restrict entry and identify boundaries of hazardous areas. Contains no lead or toxic chemicals.

#### **PRODUCT APPLICATION**

Bright yellow or red background with black lettering for high visibility for directional and/or safety to restrict entry to and identify boundaries of hazardous areas.

## INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

### **NOMINAL VALUES**

The following data are nominal values based on PSTC, ASTM and other standard tests. The data should not be considered as specifications.

Backing	Polyethylene Film
Density	0.922
Tear Strength	MD 200 ~ 250 CD 450 ~ 500
Tensile Strength (lbs/in)	MD 4500 ~ 5000 CD 450 ~ 500
Elongation (% at break)	MD 750 ~ 850 CD 800 ~ 950
Total Thickness (mil)	2 (0.058mm)



intertape polymer group®

100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA Customer Service: 800.IPG.8273 | 800.474.8273

Tape Technical Service: 877.447.4832

www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 6/09

