


Product data sheet

Characteristics

QO120M200P

Load center, QO, 1 phase, 20 spaces, 30 circuits, 200A convertible main breaker, PoN, NEMA1, UL



Main

| | |
|----------------------|-------------|
| Marketing Trade Name | QO |
| Product Type | Load Center |

Complementary

| | |
|--|------------------------------------|
| Tightening Torque | Cover: 20 lb.in |
| Load Center Type | Main breaker |
| Rated Current | 200 A |
| Number of Spaces | 20 |
| Max Short Circuit Current Rating | 22 kA |
| Maximum Number of Single Pole Circuits | 30 |
| Maximum Number of Tandem Breakers | 10 |
| Number of Phases | 1 phase |
| Ground Bar | Grounding bar (ordered separately) |
| Box Number | 9 |
| Height | 29.86 in (758.44 mm) |
| Width | 14.25 in (361.95 mm) |
| Depth | 3.75 in (95.25 mm) |

Environment

| | |
|---------------------------------------|---------------------------------|
| Enclosure Rating | NEMA 1 for indoor |
| Ambient Air Temperature for Operation | 23 °F (-5 °C) 104 °F (40 °C) |
| Product Certifications | UL Listed |

Ordering and shipping details

| | |
|-----------------------|--|
| Category | 10001 - QO PON 1PH LC,12-60 CKT, MB N1 |
| Discount Schedule | DE3A |
| GTIN | 00785901607410 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 1 lb(US) (0.45 kg) |
| Returnability | Yes |

Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |