



model 3610F

ADA Filtered Stainless Steel Outdoor Bottle Filler

FEATURES & BENEFITS

ADA COMPLIANCE

ADA-compliant bottle filling station for wheel chair use.

BOTTLE FILLER

The ADA-compliant open design bottle filling station offers a 17" high bottle area, and open sides making this push button operated bottle filling station more accessible to users.

STAINLESS STEEL VALVE

The push-button activated valve offers the only all stainless steel valve body that is machined out of solid bar stock, is fully serviceable through the front of the push button assembly offering access to the water control cartridge and integral water supply strainer, and with front access to the water stream height adjustment for easy maintenance without having to remove the valve. Operating pressure range of 30 to 90 psi (2.1 to 6.2 bar).

CONSTRUCTION

Heavy-duty stainless steel with silver powder-coated finish. Modular construction allows for easy replacement or rearrangement of drinking fountain bowls and bottle filler modules.



OPTIONS

Pet Fountain: Model 3670, dog bowl attachment for 3600 series pedestal fountains.

Hose Bib: Model 3660, lockable hose bib attachment for 3600 series pedestal fountains.

Fountain Arm: Model 3671 pedestal arm for adding the option of a bottle filler or fountain attachment.

Fountain Attachment: Model 3680, drinking fountain bowl attachment.

Fountain Attachment: Model 3690, bottle filler attachment.

Nozzle For Bottle Filler: The Haws VRKNOZ1 is a package of ten replacement nozzles for the Haws 3600 series bottle filler. Not for freeze resistant models.

Installation Aid: Model MTG.3600, mounting plate for 3600 series pedestals.

For more information, visit www.hawsc.com or call (888) 640-4297.

SPECIFICATIONS


Model 3610F outdoor, ADA pedestal mounted bottle filler shall include a heavy-duty stainless steel pedestal with matte silver powder-coating, 6428 filter with mounting bracket, push-button operated stainless steel valve with front-accessible cartridge and flow adjustment, large-opening bottle filler with quick-fill 1 gpm flow rate, 100% lead-free waterways, vandal-resistant access plates, integral mounting feet, and 1-1/2" slip waste.

APPLICATIONS


The 3610F offers a solution for the changing needs of outdoor settings as well as outdoor wheelchair access, appealing to all users through accessibility and safety. This outdoor bottle filler is ideal in areas such as parks, schools, and other outdoor areas where hydration facilities are needed. Model meets all current Federal Regulations for the disabled including those in the Americans with Disabilities Act, and complies with Prop 65. Certified by CSA to NSF/ANSI 61, section 9 and NSF/ANSI 372; and was evaluated to be compliant to US and Canada Plumbing Codes including Uniform Plumbing Code (UPC), International Plumbing Code (IPC) and National Plumbing Code of Canada (NPC).




- NOTES:
 1. WHEN INSTALLING THIS UNIT, LOCAL, STATE, OR FEDERAL CODES SHOULD BE ADHERED TO. INSTALL A TRAP IN THE WASTE LINE AND A SCREWDRIVER STOP IN THE SUPPLY LINE IF REQUIRED.



ADA COMPLIANT BOTTLE FILLER




CONCRETE ANCHORS INCLUDED. RE-USABLE TEMPLATE MODEL M.T.G. 3600 AVAILABLE, SOLD SEPARATELY.



HAWS MODEL 3610/3610F IS FULLY COMPLIANT WITH THE FEDERAL 2010 AMERICANS WITH DISABILITIES ACT (ADA) ACCESSIBILITY REQUIREMENTS WHEN INSTALLED AS SHOWN HERE AND WHEN INSTALLED WITH PROPER CLEARANCES AND ACCESS. LOCATE THE PEDESTAL BASE WITH AT LEAST 8" OF CLEAR UNOBSTRUCTED HARDSCAPE BEHIND THE PEDESTAL. IT IS THE RESPONSIBILITY OF THE INSTALLER TO ADHERE TO LOCAL, STATE, AND FEDERAL CODES WHEN INSTALLING THIS UNIT. DISTANCE TO SURROUNDING OBJECTS, APPROACH SURFACES, ETC. SHOULD BE CONSIDERED.


		1455 KLEPPE LANE SPARKS, NEVADA, 89431 (775) 359-4712 FAX (775) 359-7424 E-MAIL: HAWS@HAWSCCO.COM WEBSITE: WWW.HAWSCCO.COM	
ENCL. 5686	REV. E/CN. 5779	BY: F.V.	MODEL(S) 3610 & 3610F
DRAWN BY: F.V.	DATE: 07/21/09	CHKD. BY: B.M.	
APPROVED BY: F.V.	DATE: 09/16/21	SCALE: 1/2" = 1"	DRAWING TYPE: INSTALLATION
		SIZE: A	SHEET 1 OF 6
PART NUMBER 0510001188.D		REVISION 2	

INSTALLATION INSTRUCTIONS



STEP 2


PLACE SQUARE TRIM RING ON BOTTOM OF BOTTLE FILLER AND PLACE BOTTLE FILLER ON TOP OF PEDESTAL, FACING THE FRONT. USE 3/8" BOLTS AND NUTS VIA THE FRONT ACCESS PANEL TO SECURE BOTTLE FILLER TO PEDESTAL. CAREFULLY CENTER TRIM RING AND BOTTLE FILLER AND TORQUE BOLTS/NUTS TO 18 FT-LBS.



1455 KLEPPE LANE
 SPARKS, NEVADA, 89431
 (775) 359-4712 FAX (775) 359-7424
 E-MAIL: HAWS@HAWSCCO.COM
 WEBSITE: WWW.HAWSCCO.COM

E.C.N.	REV. E.C.N.	BY:	MODEL(S)	
5586	5779	F.V.	3610 & 3610F	
DRAWN	DATE	CHK'D		
BY	BY	BY		
APPROVED	DATE	SCALE	DRAWING TYPE	INSTALLATION
F.V.	09/16/21	1/24		SIZE: A
				SHEET 3 OF 6
				REVISION
				2
				PART NUMBER
				0510001188.D

INSTALLATION INSTRUCTIONS




MODEL 3610F (WITH FILTER) SHOWN

STEP 3

INSTALL SUPPLIED DRAIN COMPONENTS AS SHOWN. RED COMPRESSION WASHER ADAPTS FROM 1-1/4" TO 1-1/2" AT DRAIN TAIL PIECE. BLACK COMPRESSION WASHER IS USED IN TRAP ADAPTER AT COUPLER. USE APPROPRIATE PVC CEMENT TO MAKE SOLVENT CEMENT CONNECTIONS. TRIM TAIL PIECE LENGTH IF REQUIRED. NOTE THAT EXTRA PARTS MAY BE INCLUDED TO FACILITATE OTHER CONFIGURATIONS OF THIS FOUNTAIN.

		EN: 5686 REV/EN: BY: MODEL(S): DRAWN: DATE: 5/7/9 F.V. APPROVED: DATE: 1/12/02 B.M.	
		SCALE: 1/2" = 1" DRAWING TYPE: INSTALLATION SIZE: A	
1455 KLEPPE LANE SPARKS, NEVADA, 89431 (775) 359-4712 FAX (775) 359-7424 E-MAIL: HAWS@HAWSOCO.COM WEBSITE: WWW.HAWSOCO.COM		PART NUMBER: 0510001188.D	REVISION: 2

INSTALLATION INSTRUCTIONS




3610 SUPPLY PLUMBING

STEP 4

COMPLETE WATER SUPPLY PLUMBING AS SHOWN. OPEN SUPPLY VALVE AND TEST. REPLACE PEDESTAL ACCESS PLATES.

NOTE: FILTER BRACKET MOUNTS TO INSIDE OF THESE RAILS ON THE LEFT SIDE. USE THREADED HOLES SHOWN.



3610F FILTER BRACKET MOUNTING

STEP 5

INSTALL FILTER MOUNTING BRACKET (SUPPLIED WITH MODEL 6477) TO LEFT INSIDE VERTICAL RAILS USING 2 BUTTON HEAD SCREWS AS INDICATED ABOVE. INSTALL FILTER HEAD ON HANGER ANGLE WITH 4 SUPPLIED SELF-TAPPING SCREWS. INSTALL FILTER HANGER ANGLE BRACKET IN RIGHTMOST HOLES AS SHOWN. SEE MODEL 6477 OPERATION AND MAINTENANCE MANUAL FOR ADDITIONAL DETAILS.

© 2021 Haws Corporation - All Rights Reserved. HAWSCO® and other trademarks used in these materials are the exclusive property of Haws Corporation.

1455 KLEPPE LANE
SPARKS, NEVADA 89431
(775) 359-4712 FAX (775) 359-7424
E-MAIL: HAWSCO@HAWSCO.COM
WEBSITE: WWW.HAWSCO.COM


E.C.N.	REV. E.C.N.	BY:	MODEL(S)	
5686	5779	F.V.	3610 & 3610F	
DRAWN BY:	DATE:	CHK'D BY:		
APPROVED BY:	DATE:	DATE:		
F.V.	09/16/21	SCALE:	1/24	DRAWING TYPE: INSTALLATION
			SIZE:	A
			SHEET 5 OF 6	
			2	

Haws

NOTES ON OPTIONAL CONFIGURATIONS



HAWS 3600/3600F SERIES OUTDOOR FOUNTAINS ARE MODULAR AND CAN BE ASSEMBLED AND CONFIGURED MANY DIFFERENT WAYS. DISPLAYED HERE ARE A FEW EXAMPLES. CONFIGURATIONS OTHER THAN THAT SHOWN IN THE INSTALLATION INSTRUCTIONS FOR THE 3610/3610F MAY AFFECT COMPLIANCE WITH ADA REGULATIONS. IT IS THE RESPONSIBILITY OF THE INSTALLER TO UNDERSTAND LOCAL, STATE, AND FEDERAL REGULATIONS AS APPLICABLE IF INSTALLING THIS FOUNTAIN IN CONFIGURATIONS OTHER THAN THAT INDICATED ON SHEET 1 (PAGE 6 OF 11).

BOTTLE FILLER AND FOUNTAINS CAN BE INSTALLED TO FACE ANY DIRECTION



ADA ARM HEIGHT POSITION OPTIONS					
	LEFT SIDE*	RIGHT SIDE*	ARM HEIGHT (LOWER EDGE)	BUBBLER NOZZLE HEIGHT	
STANDING ADA	YES (STD)	NO	31-7/8 [809 mm]	39-3/8 [999 mm]**	
WHEELCHAIR ADA	YES	YES (STD)	27 [687 mm]	34-5/8 [878 mm]	
CHILD ADA	YES	YES	22-1/4 [566 mm]	29-7/8 [757 mm]	

* RIGHT AND LEFT CAN BE REVERSED IF PEDESTAL IS ROTATED 180°.
 **NOZZLE HEIGHT IS 41-1/2" WHEN FOUNTAIN IS INSTALLED ON TOP OF PEDESTAL.



27" [687mm]
 WHEELCHAIR ADA POSITION

1455 KLEPPE LANE
 SPARKS, NEVADA 89431
 (775) 359-4712 FAX (775) 359-7424
 E-MAIL: HAWS@HAWSCCO.COM
 WEBSITE: WWW.HAWSCCO.COM

E.C.N. 5686	REV. E.C.N. F.V.	MODEL(S)	3610 & 3610F
DRAWN BY: 5779	DATE: 07/12/01	BY: F.V.	
APPROVED: F.V.	DATE: 09/16/21	SCALE: 1/24	DRAWING TYPE: INSTALLATION
		SIZE: A	SHEET 6 OF 6
			REVISION: 2
			PART NUMBER: 0510001188.D