

PF14

SPECIALTY IDENTIFICATION PAPER FLATBACK TAPE

DESCRIPTION

A medium tensile strength, pressure-sensitive, kraft flatback, paper packaging and identification tape. Specially formulated adhesive provides for easier unwind while exhibiting an excellent balance of face-to-face adhesion and quick stick characteristics. Printable with standard flexographic ink.

PRODUCT APPLICATIONS

Designed for light-weight packaging, bag locking, decorative edging, marking and color coding.

GOVERNMENT CONFORMANCE

A-A-883, Type II. ASTM D6123, D6123M, Type II. General Motors 9885278

STORAGE RECOMMENDATION

Store new stock behind current stock. Store in a clean, dry place. Temperature of 70°F (21°C) +/- 6°F, and 40% to 50% relative humidity are recommended.

SHELF LIFE

When stored under recommended conditions, converted rolls have an expected shelf life of up to 12 months from the date of shipment. Jumbo rolls have the same expected shelf life, but it is recommended that they are converted within six (6) months of date of shipment.



100 Paramount Drive, Suite 300 | Sarasota, FL 34232 | USA
Customer Service: 800.IPG.8273 | 800.474.8273
Tape Technical Service: 877.447.4832
www.itape.com | info@itape.com

While we believe them to be reliable, the statements and information herein are only for general guidance and are not warrants or guarantees for accuracy and completeness. The user must, by test or otherwise, determine suitability for this purpose. There is no warranty of fitness for a particular purpose. Our standard term and conditions of sale apply exclusively to all orders, and all liability for damages of any kind, including consequential, exceeding purchase price is excluded. No one is authorized by us to make oral warranties. We reserve the right to make changes without notice or obligation in our products and publications.

EFFECTIVE: 12/13

INTERTAPE POLYMER GROUP® TECHNICAL DATA SHEET

NOMINAL VALUES

The following data are nominal values based on PSTC, ASTM and other standard tests. The data should not be considered as specifications.

| | |
|---|---|
| Backing | Kraft Flatback |
| Adhesive | Synthetic Rubber |
| Adhesion to Steel (oz/in of width) PSTC-101 | 50 (13.7 N/25mm) |
| Quick Stick (oz/in of width) To Kraft To Steel | 8 (2.2 N/25mm) 23 (6.3 N/25mm) |
| Tensile Strength (lbs/in of width) PSTC-131 | 31 (136 N/25mm) |
| Elongation (% at break) PSTC-131 | 3 |
| Total Thickness (mils) PSTC-133 | 6.3 (0.16mm) |
| Colors | White, Yellow, Blue, Red, Orange, Pink, Light Green |

