

# BLACK SWAN MFG. CO.

#### GHS SAFETY DATA SHEET



#### **SECTION 1 - IDENTIFICATION**

Manufacturer:

Black Swan Mfg. Co. 4540 W. Thomas St. Chicago, IL 60651-3318 Tel.: 800-252-5796 Fax: 773-227-3705

Web Site: <a href="www.blackswanmfg.com">www.blackswanmfg.com</a> E-mail: info@blackswanmfg.com

Fax: 773-227-3705

For any Transportation or Medical Chemical Emergencies call:

#### **INFOTRAC**

(800) 535-5053 **OR** (352) 323-3500

24 hours per day - 7 days a week

Product Name: Stay Soft Plumbers Putty

Recommended Use: Putty used for setting closet bowls, sink strainers and many other applications.

#### **SECTION 2 – HAZARD(S) IDENTIFICATION NFPA GHS Classification** Labels None HEALTH HAZARD FIRE HAZARD 4 – Deadly 3 - Extreme Danger 2 – Hazardous 1 - Slight Hazardous 0 - Normal Material Health **Environmental** Flash Points 4 - Below 73°F 3 - Below 100°F 2 - Above 100°F, Not exceeding 200°F 1 - Above 200°F 0 - Will not burn Acute Toxicity:Not Established Acute Aquatic Toxicity: Not Established Skin Irritation: Not Established Signal Word Eye Irritation: Not Established Chronic Aquatic Toxicity: Not Established None Skin Sensitization: NO SPECIFIC HAZARD REACTIVITY 4 – May detonate 3 – Shock and heat may detonate 2 – Violent chemical change **HMIS** Oxidizer Acid Alkali Corrosive Use NO WATER ACID ALK COR **Physical** HEALTH 0 None 1 – Unstable if heated 0 – Stable **FLAMMABILITY** 0 **Hazardous Statements Precautionary Statements** REACTIVITY None P102: Keep out of reach of children

SECTION 3 – COMPOSITION / INFORMATION ON INGREDIENTS							
Chemicals	CAS#	EINECS#	REACH	Approx %			
			Pre-registration Number				
DISTILLATES, HYDROTREATED							
LIGHT NAPHTHENIC	64742-53-6	265-156-6	N/A	5-10%			
CALCIUM CARBONATE	471-34-1	N/A	N/A	40-80%			
BENTONITE CLAY	68953-58-2	N/A	N/A	1-5%			
CANOLA OIL	129828-25-7	N/A	N/A	1-5%			
*Unlisted ingredients are not classified as hazardous	according to OSHA 1910.12	.00.					

#### **SECTION 4 – FIRST-AID MEASURES**

Inhalation: None.

Skin: Wash skin thoroughly with soap and water.

**Eyes**: Flush with water for 15 minutes. If irritation persists, get medical attention. **Ingestion**: DO NOT INDUCE VOMITING. Contact physician immediately.

#### **SECTION 5 – FIRE-FIGHTING MEASURES**

Fire Hazard: None.

Combustion Products: None.

Extinguishing Media: Carbon Dioxide Gas, Dry Chemical Powder, Water.

Unsuitable Extinguishing Media: None known.

**Protective Equipment**: None.

**Special Fire Fighting Procedures:** As appropriate for combustibles in area.

#### **GHS SAFETY DATA SHEET**

#### SECTION 6 – ACCIDENTAL RELEASE MEASURES

Personal Precautions: None.
Protective Equipment: None.
Emergency Procedures: None.
Environmental Precautions: None.

Methods for Cleaning Up: Clean up by scrapping and put in a container for disposal.

# SECTION 7 – HANDLING AND STORAGE Handling No special precautions. Storage No special precautions.

#### SECTION 8 – EXPOSURE CONTROLS / PERSONAL PROTECTION

#### **Exposure Limits**

This product is not classified as hazardous according to OSHA 1910.1200.

Engineering Controls: A source of running water to flush or wash the eyes and skin in case of contact. Use local exhaust as needed.

Ventilation: Local ventilation is adequate.

Personal Protective Equipment - Respiratory: None. Skin: None. Eyes: None.

SECTION 9 – PHYSICAL & CHEMICAL PROPERTIES							
Appearance:	Beige Putty	Flash Point:	Not Established	Vapor Pressure:	Not Established		
Odor:	Mild Petroleum	Specific Gravity:	2.14	Flammability:	Not Established		
pH:	Not Established	Solubility (H2O):	Insoluble	Flammability Limits:	LEL – Not Established		
Melting Point:	Not Established	Evaporation Rate:	Not Established		UEL – Not Established		
Freezing Point:	Not Established	Vapor Density:	Not Established				
<b>Boiling Point:</b>	Not Established	VOC:	0 g/l				

#### **SECTION 10 – STABILITY AND REACTIVITY**

Stability: Stable.

Hazardous polymerization: Will not occur.

Conditions to avoid: None.

**Incompatible materials:** Strong oxidizers.

**Hazardous decomposition products:** Carbon Dioxide and Carbon Monoxide may be released on burning.

### **SECTION 11 – TOXICOLOGICAL INFORMATION**

#### Toxicity

This product is not classified as hazardous according to OSHA 1910.1200.

Likely Routes of Exposure: Skin Contact and Ingestion.

Symptoms and Effect - Inhalation: None. Skin Contact: None. Eye Contact: None. Ingestion: None.

Long-Term Effect: None known.

Pre-Existing Conditions: None known.

#### **SECTION 12 – ECOLOGICAL INFORMATION**

Ecotoxicity: None known.

Persistance & Degradability: None known. Bioaccumulative Potential: None known.

Mobility in soil: None known.

# SECTION 13 – DISPOSAL CONSIDERATION

Dispose of product or container in accordance with federal, state or local regulations.

#### **SECTION 14 – TRANSPORTATION INFORMATION**

D.O.T. (U.S.): Not Regulated.

## **GHS SAFETY DATA SHEET**

# **SECTION 15 – REGULATORY INFORMATION**

**Precautionary Label Information:** None.

Risk Phrases: None.

Safety Phrases: S2-Keep out of reach of children.

#### **SECTION 16 – OTHER INFORMATION**

Information on this form is furnished solely for the purpose of compliance with the Occupational Safety and Health Act and shall not be used for any other purpose. Black Swan Mfg. Co. urges the customers receiving this Material Safety Data Sheet to study it carefully to become aware of the hazards, if any, of the product involved. In the interest of safety, you should notify your employees, agents and contractors of the information on the sheets.

DATE: 01/01/2021