Rheem® RTGH Series Super High Efficiency Condensing Tankless Gas Water Heaters

Easy Installation

- PVC Vent runs up to 60' (2"), 150' (3")
- Enhanced design is up to 20% smaller and lighter making one-person installs even easier

Ready for Retrofits

- Industry Best! 1/2" side to side clearance allows you to safely work in spaces the competition can't
- 1/2" Gas line compatibility (subject to local code)

Key Features

- Rheem® Exclusive! Hot-start
 Programming™ ensures the unit is in a ready state between back-to-back usage, minimizing any cold water bursts
- Built-in Wi-Fi with EcoNet® capability for direct control from your device (on select models)
- LeakGuard® All-inclusive leak detection and prevention system that detects any leak that comes from the unit (on select models)



RTGH Series Models

Indoor Models
(Outdoor Conversion Kit
Available: **RTGH-X**)
11,000-199,900 BTU/h
Natural Gas and
Liquid Propane Models*

*Swap P for N in model number for Liquid Propane model










Clearances						
Top / Bottom	12"					
Front	1/2"5					
Sides	1/2"					
Back / From Vent Pipe	0"					



¹Based on simultaneous showers using 2.5 GPM flow rate pre-mixed with cold water line. Flow rates vary depending on temperature of incoming cold water and water heater set temperature. Refer to flow rate curves for accurate sizing. ²For indoor application, this is the temperature of outdoor intake air. ³ Manifolds with standard RJ11 communication cables. ⁴If antifreeze is on and combustion is on, total W will be 217W (85+132). ⁵Recommended 24* clearance for service.


Specifications

Rheem Model Number		RTGH-68DVLN-3	RTGH-84DVLN-3	RTGH-90DVLN-3	RTGH-95DVLN-3 RTGH-95DVELN-3 (Wi-Fi Model)		
Gas Input	MAX	120,000 BTU/h	157,000 BTU/h	180,000 BTU/h	199,900 BTU/h		
Rate	MIN	11,000 BTU/h	11,000 BTU/h	11,000 BTU/h	11,000 BTU/h		
Uniform Energy	Factor (UEF)	0.90		0.93			
Gallons	MAX (35°F)	6.6	8.4	9.0	9.5		
Per Minute	45°F Rise	5.1	6.7	7.7	8.5		
(GPM)	67°F Rise	3.4	4.6	5.2	5.7		
Number of B	athrooms ¹	2.5	3	3 - 4	4		
Temp. F	Range		100°F	- 140°F			
Temp. Setting	from Factory		12	20°F			
High Temp. Availa			1	No			
Freeze Pre	otection		-30°F Air Intak	e ² , -4°F Ambient			
Installatio	on Type	Indoor (O	utdoor Conversion	Kit sold separatel	y: RTGH-X)		
Heat Exchang	ger Material	Prin	nary: Copper - Se	condary: Stainless	Steel		
Minimum Acti	vation Flow		0.4	GPM			
Minimum Cont	inuous Flow		0.26	GPM			
Maximum	Altitude	7,800 ft.					
Ultra Lo		Meets 14 ng/J NOx requirements - SCAQMD Rule 1146.2 compliant					
Warra		15 year l		5-Year Parts 1-	Year Labor		
Heig				3.7"			
Wid				7.7"			
Dep	th	9.8"					
Weight	<u> </u>			2.9			
Venting Dian			2"	/ 3"			
Max. Single (straight	pipe)			/ 150 ft (3")			
Venting M			Sched. 40 PVC, C	PVC, Polypropyler	ne		
Manifold ((max. ι			6 L	Jnits ³			
Conti	***			gital display			
Power S	Supply			/ 60Hz			
Max. P Consum			132W (Antifre	use), 0.7 Amps eeze), 1.1 Amps by), 0.03 Amps ⁴			
Gas Coni	nection		3/4	" NPT			
Hot Water C	onnection	3/4" NPT					
Cold Water (Connection	3/4" NPT					
Condensate (Connection			" NPT			
Vent Conr Diame	(Adapter required t /C from unit)	o vent					

All models are available in Natural Gas or Propane (LP). For Propane replace the N with P for LP model.



Water Heater Flow Rate Curves



Water Flow (GPM)

Temperature Rise (°F)									
Model Number	35°	45°	50°	60°	67°	70°	80°	90°	100°
RTGH-95DVL-3	9.5	8.5	7.7	6.4	5.7	5.5	4.8	4.3	3.8
RTGH-90DVL-3	9.0	7.7	6.9	5.8	5.2	4.9	4.3	3.8	3.5
RTGH-84DVL-3	8.4	6.7	6.0	5.0	4.6	4.3	3.8	3.3	3.0
RTGH-68DVL-3	6.6	5.1	4.6	4.6	3.4	3.3	2.9	2.6	2.3

Temperature Rise (°F)									
Model Number	35°	45°	50°	60°	67°	70°	80°	90°	100°
RTGH-95DVL-3	9.5	8.5	7.7	6.4	5.7	5.5	4.8	4.3	3.8
RTGH-90DVL-3	9.0	7.7	6.9	5.8	5.2	4.9	4.3	3.8	3.5
RTGH-84DVL-3	8.4	6.7	6.0	5.0	4.6	4.3	3.8	3.3	3.0
RTGH-68DVL-3	6.6	5.1	4.6	4.6	3.4	3.3	2.9	2.6	2.3
Ahove estimates are for sizing purposes only									

Venting


SINGLE UNIT: MAX. EQUIVALENT VENT LENGTHS - STRAIGHT PIPE							
Number of 90 Elbows	Max Length 2" straight pipe	Max. length 3" straight pipe					
0	60 ft. (18.3 m)	150 ft. (45.7 m)					
1	54 ft. (16.5 m)	144 ft. (43.9 m)					
2	48 ft. (14.6 m)	138 ft. (42.7 m)					
3	42 ft. (12.8 m)	132 ft. (40.2 m)					
4	36 ft. (11.0 m)	126 ft. (38.4 m)					
5	30 ft. (9.1 m)	120 ft. (36.6 m)					
6	24 ft. (7.3 m)	114 ft. (34.7 m)					

Min. Vent Length Straight Pipe				
Number of 90° Elbows	Min. Length 2" 3" pipe			
1	1.0 ft (0.3 m)			


Equivalent Ft. of Elbows						
	2" Pipe 3" Pipe					
90° Elbow	6 ft (1.83 m)	6 ft (1.83 m)				
45° Elbow	3 ft. (0.9 m)	3 ft. (0.9 m)				

Venting Materials Allowed: Schedule 40 PVC, CPVC, Polypropylene


Dimensions



TOP VIEW



BOTTOM VIEW



Hanging bracket and bird screens are included with water heater.

Parts & Accessories

Condensate Neutralizer	Recirculation Pump	Pipe Cover	Horizontal Vent Termination	Concentric Vent Termination	AllClear® Water Treatment System	Isolation Valve Kit	Manifold Cables	Outdoor Conversion Kit
SP12151 (optional)	AP17920	AP22097	2" US: SP21069G 3" US: SP21069E	2" - SP20897 3" - SP20245	RTG20251	RTG20326	RCPN-AMP03- 0013111101-0003 (48")	RTGH-X

In keeping with its policy of continuous progress and product improvement, Rheem reserves the right to make changes without notice.

Rheem Water Heating • 1115 Northmeadow Parkway, Suite 100 Roswell, Georgia 30076 • www.rheem.com

Rheem Canada Ltd./Ltée • 125 Edgeware Road, Unit 1 Brampton, Ontario L6Y 0P5 • www.rheem.com

