

**Jobber drill HSS N, TiN, Ø DC h8: 12,2mm****Order data**

Order number	114360 12,2
GTIN	4045197017161
Item class	12B

Description**Version:**

Standard core without core taper.

Precision ground point.

Profile ground:

High concentricity and pitch accuracy, drills for series production use.

With point geometry shape C from size 2.4 mm

Recommendation:**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c$$

Technical description

Nominal Ø D _c	12.2 mm
Feed f in steel < 500 N/mm ²	0.2 mm/rev.
Flute length L _c	101 mm
Number of cutting edges Z	2
Tolerance nominal Ø	h8
Shank Ø D _s	12.2 mm
Overall length L	151 mm
Standard	DIN 338
recommended maximum drilling depth L ₂	82.7 mm
Point angle	118 degrees

Shank	Plain shank
Coating	TiN
Tool material	HSS
Type	N
Helix angle	35-40 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	56 m/min	N
Alu > 10% Si	suitable only under restricted conditions	50 m/min	N
Steel < 500 N/mm ²	suitable	50 m/min	P
Steel < 750 N/mm ²	suitable	37 m/min	P
Steel < 900 N/mm ²	suitable	31 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	12 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	10 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	15 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	10 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	6 m/min	S
GG(G)	suitable	31 m/min	K
CuZn	suitable only under restricted conditions	80 m/min	N

Oil	suitable
wet maximum	suitable