

Garant
GARANT Master Alu SlotMachine solid carbide roughing end mill HPC, DLC, Ø e8 DC: 8mm

Order data

Order number	205265 8
GTIN	4062406122546
Item class	11X

Description
Version:

For roughing. Special profile for machining non-ferrous metals.

Advantage:

Optimised flute form, eccentric relief ground, generous chip spaces.

Up to $2 \times D$ into solid material at very high feed rates and smooth cutting action.

Ramping capability up to 45° .

Very high feed rates when plunging vertically, thanks to **special plunging geometry**.

Note:

For **HB shanks**: use order no. **205266**.

Technical description

No. of teeth Z	3
Helix angle	35 degrees
Tolerance nominal Ø	e8
Overhang length L_1 incl. recess	30 mm
Direction of infeed	horizontal, oblique and vertical
Feed f_z for side milling in short-chipping aluminium	0.12 mm
Balance quality with shank	G 2.5 with HA
Shank Ø D_s	8 mm
Shank	DIN 6535 HA to h6

Overall length L	68 mm
Cutting edge $\varnothing D_c$	8 mm
Recess $\varnothing D_1$	7.5 mm
Feed f_z for slot milling in short-chipping aluminium	0.1 mm
Flute length L_c	24 mm
Corner rounding r_v	0.2 mm
Series	Master Alu
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Milling profile	WR
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	$0.5 \times D$ for side milling
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	450 m/min	N
Aluminium (short chipping)	suitable	400 m/min	N
Alu > 10% Si	suitable	380 m/min	N
PA 66	suitable only under restricted conditions	120 m/min	N
PEEK	suitable only under restricted conditions	100 m/min	N

Cu	Suitable	160 m/min	N
CuZn	Suitable	200 m/min	N
wet maximum	suitable		
wet minimum	Suitable only under restricted conditions		
dry	Suitable only under restricted conditions		
Air	suitable		