

Garant**Solid carbide jobber drill extra short, uncoated, Ø DC h7: 3,25mm****Order data**

Order number	122100 3,25
GTIN	4045197771254
Item class	11E

Description**Version:****Similar to DIN 6539** (extra short).

Nominal Ø and shank Ø equal.

Note:Flute length $L_c = L_2 + 1.5 \times D_c$.

Non slip clamping in drill chuck No. 341050 with diamond coated jaws.

Technical description

Feed f in steel < 1100 N/mm ²	0.08 mm/rev.
Shank Ø D _s	3.25 mm
Tolerance nominal Ø	h7
Number of cutting edges Z	2
Flute length L _c	18 mm
Nominal Ø D _c	3.25 mm
Standard	DIN 6539
Overall length L	49 mm
recommended maximum drilling depth L ₂	13.2 mm
Coating	uncoated
Tool material	Solid carbide
Type	N

Point angle	118 degrees
Helix angle	30 degrees
Shank	Parallel shank to h7
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions	200 m/min	N
Aluminium (short chipping)	suitable	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	140 m/min	N
Steel < 500 N/mm ²	suitable	70 m/min	P
Steel < 750 N/mm ²	suitable	70 m/min	P
Steel < 900 N/mm ²	suitable	60 m/min	P
Steel < 1100 N/mm ²	suitable	40 m/min	P
Steel < 1400 N/mm ²	suitable	25 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	20 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	20 m/min	M
Ti > 850 N/mm ²	suitable	15 m/min	S
CuZn	suitable	140 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		

