

**Hand reamer set No. 160150 in a box H7, Number of reamers: 6****Order data**

Order number	160175 6
GTIN	4045197994806
Item class	120

Description**Version:**

With **left-hand helix** 7 – 8° and long taper lead, more than 1/5 of the cutting length. An even number of teeth with irregular spacing for accurately round holes, free of chatter. The cylindrical ground land on the plain cutting section smooths the hole and guides the reamer.

Application:

For through holes (not for blind holes). Also very suitable for interrupted holes.

Content:

1 pc. each hand reamer: Size 3; 4; 5; 6; 8; 10

Supplied with:

6-piece hand reamer set in a box.

Technical description

Number of reamers	6
Hole tolerance	H7
Tool material	HSS
Standard	DIN 206 B

Helix angle	7-8 degrees
Application for type of drilling	for through holes
Type of product	Phillips bit

Accessories

Hand reamerH7 Nominal Ø DC 6 mm	160150 6
Hand reamerH7 Nominal Ø DC 10 mm	160150 10
Hand reamerH7 Nominal Ø DC 5 mm	160150 5
Hand reamerH7 Nominal Ø DC 8 mm	160150 8
Hand reamerH7 Nominal Ø DC 3 mm	160150 3
Hand reamerH7 Nominal Ø DC 4 mm	160150 4