

Garant
Solid carbide milling cutter, uncoated, Ø e8 DC: 16mm

Order data

Order number	202810 16
GTIN	4045197662699
Item class	11X

Description
Version:

Double relief ground side clearance angle.

Technical description

Feed f_z for side milling in steel < 900 N/mm ²	0.1 mm
Cutting edge Ø D_c	16 mm
Feed f_z for slot milling in steel < 900 N/mm ²	0.08 mm
Corner chamfer width at 45°	0.15 mm
Shank form	HB
No. of teeth Z	4
Shank Ø D_s	16 mm
Overall length L	125 mm
Flute length L_c	50 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6
Tolerance nominal Ø	e8
Helix angle	35 degrees
Corner chamfer angle	45 degrees
Coating	uncoated

Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Cutting width a_e for milling operation	$0.3 \times D$ for side milling
Through-coolant	no
Colour ring	without
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	105 m/min	N
Steel < 500 N/mm ²	suitable	70 m/min	P
Steel < 750 N/mm ²	suitable	60 m/min	P
Steel < 900 N/mm ²	suitable	55 m/min	P
Steel < 1100 N/mm ²	suitable	35 m/min	P
Steel < 1400 N/mm ²	suitable	30 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	25 m/min	H
INOX < 900 N/mm ²	suitable	40 m/min	M
GG(G)	suitable	55 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		