



Solid carbide milling cutter, TiAlN, Ø DC: 16mm



Order data

Order number	202545 16
GTIN	4045197117373
Item class	12X

Description

Version:

Extra sharp cutting edges.

Dimensions similar to DIN 6527.

Eccentric relief ground.

Technical description

No. of teeth Z	4
Cutting edge Ø D _c	16 mm
Feed f _z for slot milling in short-chipping aluminium	0.065 mm
Feed f _z for side milling in short-chipping aluminium	0.12 mm
Shank Ø D _s	16 mm
Overall length L	92 mm
Flute length L _c	36 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HA to h6
Tolerance nominal Ø	e8
Helix angle	45 degrees
Corner chamfer angle	90 degrees
Coating	TiAlN

Tool material	Solid carbide
Standard	DIN 6527
Type	W
Cutting width a_e for milling operation	0.25×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	suitable	300 m/min	N
Aluminium (short chipping)	suitable	280 m/min	N
Alu > 10% Si	suitable	200 m/min	N
PMMA acrylic	Suitable	180 m/min	N
PE-HD	Suitable	130 m/min	N
PA 66	Suitable	150 m/min	N
PEEK	Suitable	130 m/min	N
PF 31	Suitable	110 m/min	N
Honeycomb sandwich	Suitable	180 m/min	N
Cu	Suitable	120 m/min	N
CuZn	Suitable	150 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable only under restricted conditions		

Services

Shank grinding Type HB

129100 HB