



## Blind hole machine taps + tapping drills, for metric threads: M3-12



### Order data

Order number	146925 M3-12
GTIN	4045197649720
Item class	12K

### Description

#### Version:

When the case is opened, the tools raise up vertically and can easily be selected.

Consisting of machine taps M3; M4; M5; M6; M8; M10; M12 and tapping drills size 2.5; 3.3; 4.2; 5; 6.8; 8.5; 10.2.

#### Content:

1 pc. each machine tap M3 – M12 No. 135855 and tapping drill No. 114405

### Technical description

for metric threads	M3 – M12
Thread type	M
Flank angle	60 degrees
Standard	DIN 371
Standard	DIN 376
Colour ring	green

Type of product	Tap
-----------------	-----

## Accessories

Machine tapHSS-E Form C M M12	135855 M12
Machine tapHSS-E Form C M M10	135855 M10
Machine tapHSS-E Form C M M6	135855 M6
Jobber drill HSS-EN Ø DC h8 10,2 mm	114405 10,2
Machine tapHSS-E Form C M M3	135855 M3
Jobber drill HSS-EN Ø DC h8 4,2 mm	114405 4,2
Jobber drill HSS-EN Ø DC h8 5 mm	114405 5
Machine tapHSS-E Form C M M4	135855 M4
Machine tapHSS-E Form C M M8	135855 M8
Machine tapHSS-E Form C M M5	135855 M5
Jobber drill HSS-EN Ø DC h8 2,5 mm	114405 2,5
Jobber drill HSS-EN Ø DC h8 6,8 mm	114405 6,8
Jobber drill HSS-EN Ø DC h8 3,3 mm	114405 3,3
Jobber drill HSS-EN Ø DC h8 8,5 mm	114405 8,5
Empty case Type 4	146961 4