

Garant**Countersink set, long No. 150371 in a case 90°, Number of countersinks: 6**

Order data

| | |
|--------------|---------------|
| Order number | 150373 6 |
| GTIN | 4045197086228 |
| Item class | 11M |

Description

Version:

Handy for assembly and workshop use.

Countersink No. 150371, **with long shank.****Content:**

1× each countersink: Size 6.3; 8.3; 10.4; 12.4; 16.5; 20.5

Supplied with:

6-piece countersink set in a case.

Technical description

| | |
|---------------------------|-------------------------|
| Number of countersinks | 6 |
| Number of cutting edges Z | 3 |
| Countersink tip angle | 90 degrees |
| Tool material | HSS |
| Standard | Manufacturer's standard |
| Shank | Plain shank with h9 |

| | |
|-----------------|-------------------------------|
| Colour ring | without |
| Type of product | Stepped drill and countersink |

User data

| | Suitability | V _c | ISO code |
|-------------------------------|---|----------------|----------|
| Alu plastics | suitable | 70 m/min | N |
| Aluminium (short chipping) | suitable | 33 m/min | N |
| Alu > 10% Si | suitable only under restricted conditions | 20 m/min | N |
| Steel < 500 N/mm ² | suitable | 28 m/min | P |
| Steel < 750 N/mm ² | suitable | 27 m/min | P |
| Steel < 900 N/mm ² | suitable only under restricted conditions | 27 m/min | P |
| wet maximum | suitable | | |
| dry | suitable only under restricted conditions | | |

Accessories

| | |
|---|-------------|
| High-precision countersink, long90° External Ø Dc 16,5 mm | 150371 16,5 |
| High-precision countersink, long90° External Ø Dc 10,4 mm | 150371 10,4 |
| High-precision countersink, long90° External Ø Dc 8,3 mm | 150371 8,3 |
| High-precision countersink, long90° External Ø Dc 20,5 mm | 150371 20,5 |
| High-precision countersink, long90° External Ø Dc 6,3 mm | 150371 6,3 |
| High-precision countersink, long90° External Ø Dc 12,4 mm | 150371 12,4 |