

Garant
Hand tap set, uncoated, M: M4

Order data

Order number	130400 M4
GTIN	4045197066237
Item class	11G

Description
Version:

Set of three, **consisting of taper, second, and plug tap. Taper tap with long pilot.**

Thread type: M

Tool material: HSS E

Standard: DIN 352

Tolerance class: ISO 2 6H

Thread pitch: 0.7 mm

Overall length L: 45 mm

Shank $\varnothing D_s$: 4.5 mm

Shank square \square : 3.4 mm

Tapping hole \varnothing : 3.3 mm

Technical description

Tapping hole \varnothing	3.3 mm
Thread pitch	0.7 mm
Thread \varnothing	4 mm
Standard	DIN 352
Shank $\varnothing D_s$	4.5 mm
Overall length L	45 mm

Shank square <input type="checkbox"/>	3.4 mm
Tolerance class	ISO 2 6H
Tool material	HSS E
Thread depth	8 mm
Thread type	M
Thread size	M4
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	A
Taper lead form	C
Taper lead form	D
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Hand tap
Colour ring	without
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu > 10% Si	suitable only under restricted conditions		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1100 N/mm ²	suitable only under restricted conditions		

INOX < 900 N/mm ²	suitable
INOX > 900 N/mm ²	suitable only under restricted conditions
Ti > 850 N/mm ²	suitable
GG(G)	suitable only under restricted conditions
Uni	suitable
Oil	suitable
dry	suitable only under restricted conditions