

Garant**Centre drill HSS-E, extra long A, uncoated, Nominal Ø DC k12: 3,15mm****Order data**

Order number	111300 3,15
GTIN	4045197000583
Item class	11A

Description**Version:**

Ground from solid and relief-ground.

Spiral fluted, extra long shank, similar to DIN 333-A.

Technical description

Number of cutting edges Z	2
for workpiece Ø	30 – 40 mm
Nominal Ø D _C	3.15 mm
Feed f in steel < 900 N/mm ²	0.03 mm/rev.
Shank tolerance	h7
Shank Ø D _s	10 mm
Overall length L	120 mm
Coating	uncoated
Tool material	HSS E
Standard	Manufacturer's standard
Type	A
Tolerance nominal Ø	k12
Countersink angle	60 degrees
Cutting direction	right-hand
Shank	Parallel shank to h7

Through-coolant	no
Colour ring	without
Type of product	Centre drill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	70 m/min	N
Aluminium (short chipping)	suitable	45 m/min	N
Steel < 500 N/mm ²	suitable	40 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	10 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
INOX < 900 N/mm ²	suitable	12 m/min	M
INOX > 900 N/mm ²	suitable	8 m/min	M
GG(G)	suitable only under restricted conditions	25 m/min	K
CuZn	suitable	80 m/min	N
Oil	suitable		
wet maximum	suitable		