

Garant
Solid carbide milling cutter DIN 6535 HB, uncoated, Ø e8 DC: 14mm


Order data

Order number	202510 14
GTIN	4045197117267
Item class	11X

Description

Version:

Extra sharp cutting edges.

Dimensions similar to DIN 6527.

Double relief ground side clearance angle.

Technical description

Overhang length L_1 incl. recess	35 mm
Feed f_z for slot milling in short-chipping aluminium	0.05 mm
Cutting edge Ø D_c	14 mm
No. of teeth Z	4
Recess Ø D_1	13.8 mm
Feed f_z for side milling in short-chipping aluminium	0.07 mm
Shank Ø D_s	14 mm
Overall length L	83 mm
Flute length L_c	30 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6
Tolerance nominal Ø	e8
Helix angle	45 degrees

Corner chamfer angle	90 degrees
Coating	uncoated
Tool material	Solid carbide
Standard	DIN 6527
Type	W
Cutting width a_e for milling operation	0.5×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	180 m/min	N
Aluminium (short chipping)	suitable	140 m/min	N
Alu > 10% Si	suitable	105 m/min	N
PMMA acrylic	Suitable	180 m/min	N
PE-HD	Suitable	130 m/min	N
PA 66	Suitable	150 m/min	N
PEEK	Suitable	130 m/min	N
PF 31	Suitable	110 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	180 m/min	N
Cu	Suitable	140 m/min	N
CuZn	Suitable	180 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		

dry	suitable only under restricted conditions
Air	suitable only under restricted conditions